

## Han 16B Easy Hood



Image is for illustration purposes only. Please refer to product description.

Part number	11 30 016 0520
Specification	Han 16B Easy Hood
HARTING eCatalogue	<a href="https://b2b.harting.com/11300160520">https://b2b.harting.com/11300160520</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® Easy Hood
Type of hood/housing	Hood

### Version

Size	16 B
Version	Side entry
Number of cable entries	1
Cable entry	1x Integrated
Locking type	Double locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP54
Type rating acc. to UL 50 / UL 50E	4
	4X
	12
Cable diameter	20 ... 34 mm

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
	Nickel
	Naphthalene
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3)
	R7 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	440 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140110816
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors