


PXMBNI16RPM06ASCM16 Datasheet



Product Name // M16 Series A Code Brass Nickel Plated
Rear Panel Mount Connector 6 Contact Pins

View Product Page



// Product Description:	
M16 Series Panel Mount Connectors	Pin or Socket
Water and dustproof to IP67 when mated with compatible connector	3, 4, 5, 6, 8, 12 Contact
A Code	Solder Terminals
Rear Panel Mount	Mate with M16 Series Inline Body and Flex Body Connectors, depending on part code

// General Information:	
Product Display Title:	M16 Series Panel Mount Connectors
Product Family:	Circular Automation Connectors
Product Series:	M16 Series
Change Notes:	PRODUCT-MOQ-ADJUSTMENT
Body Material:	Brass - Nickel Plated
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	5A
Diameter Over Coupling Ring Mm:	18.5mm
Function:	Rear Panel Mount Connector
Ip Rating:	IP67
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	6 Contacts
Pin Layout Code:	A Code
Thread Size:	M16 x 0.75
Voltage Max:	125V

// Product PDF Links

M16 Series automation connectors...

// Product 3D CAD Model Links

PXMBNI16RPM06ASCM163D CAD Model