




- NOTES:
- 1. CRIMP CONTACTS SUPPLIED UNASSEMBLED AND WITHOUT EPOXY BACKING.
 - 2. REFER TO DRAWING HPSFMISTD FOR CONTACT PATTERNS.
 - 3. HEX-NUT TORQUE: 10-12 IN-LB.
 - 4. DIMENSIONS ARE REFERENCE ONLY, IN INCHES [mm], WITHIN ±0.015 UNLESS OTHERWISE NOTED.




CRIMP CONTACTS
SF7980-18SG-300 SHOWN




FACE VIEW
SF7982-18SG-300 SHOWN




SOLDER CONTACTS
SF7982-18SG-300 SHOWN



WIRING END
SF7982-18SG-300 SHOWN



RECOMMENDED PANEL CUT-OUT



PC TAIL CONTACTS
SF7984-18SG-3ES SHOWN


PANEL-MOUNT CONNECTOR PART NUMBERS:

S F 7 9 8 X - X S G - 3 X X

EPOXY BACKING:
3ES = WITH EPOXY
300 = WITHOUT EPOXY

OF CONTACTS: 9 - 18

CONTACTS STYLE:
0 = CRIMP
2 = SOLDER
4 = PC TAIL



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

0A	PNK	1-30-18	DRAWING CREATED PER PDR17011				
REV.	INIT.	DATE	DESCRIPTION				
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED. ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 ▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			ORIG. DRAWN BY: PNK	DATE: 1-30-18	CONXall 601 E. WILDWOOD VILLA PARK, IL 60181		
			CHECKED BY:				
			APPROVED BY:	TITLE: PANEL-MOUNT CONNECTOR (9-18) #26 SOCKET CONTACTS SHIELDED MINI-CON-X STANDARD PRODUCT			
			SCALE NTS	SIZE B	SHEET 1 OF 1	CUSTOMER:	
			FILE: SF798X-XSG-3XX_CD	DIRECTORY: SLW	PART NUMBER: SF798X-XSG-3XX	REV 0A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[SF7984-15SG-3ES](#) [SF7984-18SG-3ES](#) [SF7980-12SG-300](#) [SF7980-15SG-300](#) [SF7980-18SG-300](#) [SF7982-12SG-300](#) [SF7982-15SG-300](#) [SF7982-18SG-300](#) [SF7984-12SG-3ES](#)