


1 2 3 4 5 6 7 8 9


G

G




F

F




E

E



D

D



C

C

## SPECIFICATIONS

Current Rating: 0.75 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40° to +105°  
 Insulator Material: Polyester (UL94V-0)  
 Contact Material: Phosphor bronze  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240° C for 30–60 seconds  
 (260° C for 5 seconds)

## RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)



深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°

X.X : ±0.25 X.X° : ±1°

X.XX: ±0.20 X.XX° : ±0.5°

DRAWN NAME: HX PM1.0-2x10P TP

SIZE	A4	SCALE	N:1	PROJECT NO.			
REV	A	UNIT	mm	PROJECT		PAGE	1/1