

NOTES:



1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS ARE INSTALLED INTO CONNECTOR.
3. ALL DIMENSIONS ARE REFERENCE UNLESS OTHERWISE STATED.
4. SEE DRAWING HPMISTD FOR HOLE PATTERNS.

ASSY P/N	GROMMET FOR CABLE O.D.
8282-XPG-3DC	DAISY CHAIN
8282-XPG-311	0.09-0.14 [2.3-3.5mm]
8282-XPG-315	0.15-0.17 [3.8-4.3mm]
8282-XPG-318	0.18-0.20 [4.6-5.1mm]
8282-XPG-321	0.21-0.23 [5.3-5.8mm]

KIT P/N	NO. OF CONTACTS
8282-2PG-3XX	(2)-#20
8282-3PG-3XX	(3)-#20
8282-4PG-3XX	(4)-#20
8282-5PG-3XX	(5)-#20
8282-6PG-3XX	(6)-#20
8282-7PG-3XX	(7)-#20
8282-8PG-3XX	(8)-#20
8282-XPG-3XX	

GROMMET SIZE FOR
SINGLE GROMMET OR
"DC" FOR DAISY CHAIN

NO. OF CONTACTS

GROMMET, DAISY CHAIN
FOR 8282-XPG-3DC
MAT'L: RUBBER, BLACK

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL
INFORMATION PROPRIETARY TO CONXALL
CORPORATION. ANY REPRODUCTION,
DISCLOSURE, OR USE OF THIS
DOCUMENT /INFORMATION IS EXPRESSLY
PROHIBITED UNLESS AUTHORIZED IN
WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

DIMENSIONS IN BRACKET [] ARE METRIC.

RoHS COMPLIANT

B	JD	10-13-17	UPDATED CONNECTOR AND PIN HEIGHT PER ECR 9020	
A	AN	11-03-11	DRAWING CREATED PER DOR 11-E149SL	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: AN DATE: 11-01-11	 601 E. WILDWOOD VILLA PARK, IL 60181
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 — CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			CHECKED BY:	
			APPROVED BY:	TITLE: CABLE TO CABLE CONN. ASS'Y (2-8) #20 PIN CONTACTS, SOLDER MINI-CON-X
			SCALE: NTS SIZE: B SHEET: 1 OF 1	CUSTOMER: STANDARD PRODUCT
			FILE: 8282-XPG-3XX DIRECTORY: SLW	PART NUMBER: 8282-XPG-3XX REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[8282-4PG-3DC](#) [8282-6PG-3DC](#) [8282-2PG-3DC](#) [8282-5PG-3DC](#) [8282-3PG-3DC](#) [8282-2PG-311](#) [8282-2PG-315](#)
[8282-2PG-318](#) [8282-2PG-321](#) [8282-2PG-3XX](#) [8282-3PG-311](#) [8282-3PG-315](#) [8282-3PG-318](#) [8282-3PG-321](#) [8282-](#)
[3PG-3XX](#) [8282-4PG-311](#) [8282-4PG-315](#) [8282-4PG-318](#) [8282-4PG-321](#) [8282-5PG-311](#) [8282-5PG-315](#) [8282-5PG-](#)
[318](#) [8282-5PG-321](#) [8282-5PG-3XX](#) [8282-6PG-311](#) [8282-6PG-315](#) [8282-6PG-318](#) [8282-6PG-321](#) [8282-6PG-3XX](#)
[8282-7PG-311](#) [8282-7PG-315](#) [8282-7PG-318](#) [8282-7PG-321](#) [8282-7PG-3DC](#) [8282-7PG-3XX](#) [8282-8PG-311](#) [8282-](#)
[8PG-315](#) [8282-8PG-318](#) [8282-8PG-321](#) [8282-8PG-3DC](#) [8282-8PG-3XX](#)