




Notes 1 : Lead co-planality include reinforced metal fittings shall be 0.1mm MAX.
2 : If there are pattern and a bia hole on part, there is a possibility that it will make contact with the leads.

Part No.	Number of contacts	Code No.	A	B	C	D
DF13E-10DP-1.25V(65)	10	CL536-0566-0-65	12.1	5.0	7.5	8.7
DF13E-20DP-1.25V(65)	20	CL536-0567-0-65	18.35	11.25	13.75	14.95
DF13E-30DP-1.25V(65)	30	CL536-0568-0-65	24.60	17.50	20.00	21.20
DF13E-40DP-1.25V(65)	40	CL536-0569-0-65	30.85	23.75	26.25	27.45

2	Brass	Contact area:Gold plated 0.2μm MIN	5	Elastomer	Gray
		Lead area:Tin plated 1μm MIN	4	R. PVC	Electrostatic protection. Clear
		Under plating:Nickel 1μm MIN	3	Phosphor bronze	Tin plated 1μm MIN
1	Polyamide	Beige. UL94V-0	FINISH . REMARKS		
NO. MATERIAL		FINISH . REMARKS		NO. MATERIAL	
UNITS mm		SCALE 5 : 1	COUNT	DESCRIPTION OF REVISIONS	DESIGNED
		APPROVED : HS. OKAWA	20200330	DRAWING NO.	EDC-367983-65-00
		CHECKED : TS. KUMAZAWA	20200330	PART NO.	DF13E-*DP-1.25V(65)
		DESIGNED : HK. HAYASHI	20200330	CODE NO.	CL536-
		DRAWN : DS. HIROWATARI	20200326		
					1/2

