





8		7		6		5		4		3		2		1	
<															



- Notes:
1. Material/材质: C2680 T=0.40mm;
 2. Finish/表面处理: Sn-Plated
 3. Contact surface should not have burrs, Other areas burr 0.10mm Max.
端子接触面不能有毛刺, 其他区域毛刺不能超过0.10mm
 4. Harmful material please follow RoHS / 产品需符合RoHS标准.
 5. Order information 编码原则: 925-090-10X1

See table-1/见表-1


P/N	DIM"C"	适用线径 (铜线直径范围)	表面处理
925-090-1001	0.26	27~23AWG (ø0.36 ~ ø0.57mm)	镀镍30~80u", 镀雾锡40~120u"
925-090-1011	0.31	25~22AWG (ø0.45 ~ ø0.64mm)	镀镍30~80u", 镀雾锡40~120u"
925-090-1021	0.14	31~28AWG (ø0.23 ~ ø0.32mm)	镀镍30~80u", 镀雾锡40~120u"

X, ± 0.35	X, ° ± 3°
.X ± 0.25	.X ° ± 2°
.XX ± 0.15	.XX ° ± /
.XXX ± 0.05	.XXX ° ± /
UNITS:	mm

The information in this document is property of JIDCON company and should not be copied or reproduced in any other way, without written permission.



Guangdong JiDe Precision Electronics Co., Ltd
广东济德精密电子有限公司

TITLE: Poke-in terminal	PART NO. 925-090-10X1						
APPD:	DWG NO: C-925-090-10X1						
CHKD:	 <table border="1"> <tr> <td>SCALE</td> <td>SHEET</td> <td>REV.</td> </tr> <tr> <td>N/A</td> <td>1/1</td> <td>A0</td> </tr> </table>	SCALE	SHEET	REV.	N/A	1/1	A0
SCALE	SHEET	REV.					
N/A	1/1	A0					
DRAW:							