

804-030

Series 804 Push-Pull High Speed Mighty Mouse
Jam-Nut Mount #23 PCB or Solder Cup Receptacle
Crimp Rear Release • Ordering Information

High Speed
Mighty Mouse

**Series 804 Printed
Circuit Board Receptacle**






Panel Mount Receptacles feature factory-installed non-removable contacts. Choose solder cup or printed circuit board terminals. Available in front or rear panel mount versions.

Water Immersion, Unmated

Specify **8040-005** connectors for applications where open face water immersion is not a requirement. For MIL-STD-810 Method 512G immersion requirements, specify **804-020** watertight connectors. These 804-020 connectors are specially sealed ("MOD-518") and are 100% tested to maintain a helium leak rate of 1×10^{-4} cc/second at one atmosphere pressure differential from -40C to +70C.

HOW TO ORDER

Sample Part Number


804-030	-07	M	6-4	P	N
Series	Shell Style	Shell Material / Finish	Shell Size- Insert Arrangement	Contact Style	Shell Key Position
804-005 Receptacle for Solder Cup or PCB Termination, With Standard Epoxy Potting	 - 00 Jam Nut, Front Panel	C Aluminum / Black Anodize (Non-Conductive) RoHS Compliant M Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Olive Drab Cadmium over Electroless Nickel Finish ZN Aluminum / Zinc-Nickel over Electroless Nickel ZNU Aluminum / Zinc-Nickel Black over Electroless Nickel Z1 Stainless Steel / Passivate RoHS Compliant ZB Stainless Steel / Olive Drab Chromate over Cadmium ZC Stainless Steel / Zinc Cobalt Alloy / Black Chromate	 6 - 4  6 - 7  7 - 10  9 - 19  10-26	Connector supplied with contacts P Pin, PC Tail S Socket, PC Tail E Pin, Solder Cupl F Socket, Solder Cup	Omit for Single Master Key A Pos. A (Normal) B Pos. B C Pos. C D Pos. D E Pos. E F Pos. F

Dimensions in Inches (millimeters) are subject to change without notice.



804-030-07

Series 804 Push-Pull High Speed Mighty Mouse Rear Mount Jam-Nut #23 PCB or Solder Cup Receptacle Rear Mount Crimp Rear Release • Ordering Information



Rear Panel Jam Nut
804-030-07

DIMENSIONS

Shell Size	$\varnothing A$		$\varnothing B$		C Flat		D Threads	$\varnothing E$		$\varnothing F$		$\varnothing F$ Tail Dia.
	In.	mm.	In.	mm.	In.	mm.		In.	mm.	In.	mm.	
6	.730	18.54	.625	15.87	.467	14.40	.5000-32 UN-2A	.330	8.38	.483	12.27	.018/.022 (.46/.56)
7	.910	23.11	.750	19.05	.594	15.09	.6250-28 UN-2A	.432	10.97	.570	14.48	
9	1.000	25.40	.812	20.62	.655	16.64	.6875-28 UN-2A	.551	14.00	.685	17.40	
10	1.085	27.48	.875	22.22	.721	18.31	.7500-28 UN-2A	.620	15.75	.725	18.42	

ALTERNATE KEY POSITIONS

	Pos.	A°		B°	
		In.	mm.	In.	mm.
	A	150°	210°		
	B	75°	210°		
	C	95°	230°		
	D	140°	275°		
	E	75°	275°		
	F	95°	210°		

REAR MOUNT JAM NUT PANEL CUTOUT

Shell Size	M Flat		$\varnothing N$	
	In.	mm.	In. $\pm .005$	mm. ± 0.13
6	.479 .475	12.17 12.07	.510	12.95
7	.606 .602	15.39 15.29	.635	16.13
9	.667 .663	16.94 16.84	.698	17.73
10	.734 .729	18.64 18.52	.760	19.30


Dimensions in Inches (millimeters) are subject to change without notice.

804-030-00

Series 804 Push-Pull High Speed Mighty Mouse
Front Mount Jam-Nut #23 PCB or Solder Cup Receptacle
Crimp Rear Release • Ordering Information



High Speed
Mighty Mouse



Front Panel Jam Nut
804-030-00

DIMENSIONS										
Shell Size	$\varnothing A$		B Threads	$\varnothing C$		$\varnothing D$		E Flat		$\varnothing F$ Tail Dia.
	In.	mm.		In.	mm.	In.	mm.	In.	mm.	
6	.885	22.48	.5625-28 UN-2A	.330	8.38	.688	17.47	.530	13.46	.018/.022 (.46/.56)
7	.995	25.27	.6875-28 UN-2A	.432	10.97	.812	20.62	.663	16.84	
9	1.075	27.31	.7500-28 UN-2A	.551	14.00	.875	22.22	.720	18.29	
10	1.140	28.95	.8125-28 UN-2A	.620	15.75	.938	23.82	.788	20.02	

ALTERNATE KEY POSITIONS

	Pos.	A°	B°
	A	150°	210°
	B	75°	210°
	C	95°	230°
	D	140°	275°
	E	75°	275°
	F	95°	210°

FRONT MOUNT JAM NUT PANEL CUTOUT

Shell Size	P Flat		$\varnothing R$	
	In. ± .002	mm. ± 0.05	In. ± .005	mm. ± 0.13
6	.542 .538	13.77 13.67	.575	14.61
7	.676 .671	17.17 17.04	.698	17.73
9	.732 .728	18.59 18.49	.760	19.30
10	.801 .796	20.35 20.22	.822	20.88

Dimensions in Inches (millimeters) are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[804-005-00C6-7E](#) [804-005-07M10-26S](#) [804-005-07M9-19S](#) [804-005-07ZNU10-26P](#) [804-005-07ZNU6-7P](#) [804-005-07ZNU9-19P](#) [804-005-00M7-10S](#) [804-005-07M7-10P](#) [804-005-07NF7-10P](#) [804-005-07NF7-10S](#) [804-005-07ZNU6-4S](#) [804-005-00C10-26P](#) [804-005-00M7-10P](#) [804-005-00ZNU10-26S](#) [804-005-00ZNU6-4P](#) [804-005-00ZNU6-7P](#) [804-005-00ZNU7-10P](#) [804-005-00ZNU9-19S](#) [804-005-07C6-7S](#) [804-005-07M10-26P](#) [804-005-07M6-4P](#) [804-005-07M6-7P](#) [804-005-07M9-19P](#) [804-005-07ZNU10-26S](#) [804-005-07ZNU6-7SC](#) [804-005-07ZNU9-19S](#) [804-005-07M10-26FB](#)