






REV	DESCRIPTION	DESIGN	APPROVAL	DATE
A0	NEW VERSION	Colinye	Jerry	2023/12/13



- NOTES:
1. Material/材质: See table-1/见表-1;
 2. Finish/表面处理: See table-1/见表-1;
 3. Wire size range/线规: AWG#22-#24; O.D. $\phi 1.50$ Max.;
 4. Contact surface should not have burrs, Other areas burr 0.10mm Max.
端子接触面不能有毛刺, 其他区域毛刺不能超过 0.10mm ;
 5. Harmful material please follow RoHS/产品需符合RoHS标准;
 6. Applicable Housing/适配塑壳 961-XX1X-014;
 7. Order Information/编码原则: 922-050-1031

												B	
NO		P/N		Material/材质				Finish/表面处理					
1		922-050-1031		Copper Alloy/铜合金				Tin-Plated/镀锡					
X. ± 0.35		X.° ± 5°		 Guangdong JiDe Precision Electronics Co., Ltd 广东济德精密电子有限公司								A	
.X ± 0.25		.X° ± 3°											
.XX ± 0.15		.XX° ± /											
.XXX ± 0.05		.XXX° ± /											
UNITS:		mm		TITLE: 0.50mm FEMALE TERMINAL				PART NO. 922-050-1031					
The information in this document is property of JIDCON company and should not be copied or reproduced in any other way, without written permission.				APPD:				DWG NO: C-922-050-1031					
				CHKD:									
				DRAW:									
												SCALE 8:1	SHEET 1/1
4		3		2				1					