



Pushing Performance
Since 1945

M12 Power PCB female S - box



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 309 2400
Specification	M12 Power PCB female S - box
HARTING eCatalogue	https://b2b.harting.com/21033092400

Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	PCB adapter
Specification	Straight

Version

Termination method	Reflow soldering termination (THR)
Gender	Female
Shielding	Shielded
Number of contacts	4
Number of power contacts	3
Number of special contacts	1
Specification of special contacts	PE contact
Coding	S-coding
Details	Order housings separately
Pack contents	30 pieces in a carton box

Technical characteristics

Rated current	12 A
Rated voltage	630 V
Rated impulse voltage	6 kV
Pollution degree	3



Pushing Performance
Since 1945

Technical characteristics

Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 100
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	Polyamide (PA)
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

Specifications and approvals

Specifications	IEC 61076-2-111
----------------	-----------------

Commercial data

Packaging size	30
Net weight	7.4 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140228566



Pushing Performance
Since 1945

Commercial data

ETIM	EC002637
eCl@ss	27460201 PCB connector (board connector)