





CONNECTOR DESIGNATORS A-F-H-L-S ROTATABLE COUPLING





**STYLE 2
(STRAIGHT
See Note 1)**



**STYLE 2
(45° & 90°
See Note 1)**



Termination Area
Nickel Plated
Knurl or Ridges
Mfr's Option



Polysulfide Stripes
P Option

447-425
EMI/RFI Non-Environmental Band-in-a-Can Backshell
with Cable Clamp Strain-Relief
Rotatable Coupling - Standard Profile



See inside back cover fold-out or pages 13 and 14 for Tables I and II.

TABLE III: ELBOW DIMENSIONS									
Shell Size		E		F		G		H	
Conn. Desig.									
A-F-L-S	H	Max		Max		Max		Max	
08	09	.639	(16.2)	1.380	(35.1)	.750	(19.1)	1.500	(38.1)
10	11	.664	(16.9)	1.410	(35.8)	.810	(20.6)	1.550	(39.4)
12	13	.688	(17.5)	1.430	(36.3)	.870	(22.1)	1.610	(40.9)
14	15	.705	(17.9)	1.460	(37.1)	.920	(23.4)	1.680	(42.7)
16	17	.732	(18.6)	1.480	(37.6)	.980	(24.9)	1.740	(44.2)
18	19	.748	(19.0)	1.490	(37.8)	1.020	(25.9)	1.760	(44.7)
20	21	.773	(19.6)	1.510	(38.4)	1.080	(27.4)	1.820	(46.2)
22	23	.800	(20.3)	1.550	(39.4)	1.140	(29.0)	1.900	(48.3)
24	25	.823	(20.9)	1.580	(40.1)	1.200	(30.5)	1.970	(50.0)

TABLE IV: CABLE ENTRY								
Dash	K		L		Cable Range			
No.	±.030	±(.8)	Max		Min		Max	
10	.220	(5.6)	1.000	(25.4)	.130	(3.3)	.250	(6.4)
12	.310	(7.9)	1.250	(31.8)	.250	(6.4)	.380	(9.7)
14	.440	(11.2)	1.340	(34.0)	.310	(7.9)	.440	(11.2)
16	.560	(14.2)	1.470	(37.3)	.375	(9.5)	.630	(16.0)
18	.630	(16.0)	1.560	(39.6)	.560	(14.2)	.690	(17.5)
20	.750	(19.1)	1.620	(41.1)	.630	(16.0)	.750	(19.1)
22	.880	(22.4)	1.750	(44.5)	.750	(19.1)	.880	(22.4)
24	1.000	(25.4)	1.870	(47.5)	.880	(22.4)	1.000	(25.4)
28	1.060	(26.9)	1.970	(50.0)	1.000	(25.4)	1.130	(28.7)
32	1.190	(30.2)	2.090	(53.1)	1.130	(28.7)	1.250	(31.8)

1. When maximum cable entry (page 21) is exceeded, Style 2 will be supplied. Dimensions E, F, G, and H will not apply. Please consult factory.
2. Metric dimensions (mm) are indicated in parentheses.
3. Consult factory for shorter lengths on straight backshells.
4. Backshells supplied with 600-052-* band, see Glenair Series 600 Tool Catalog for installation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[447HH425M2320-B](#) [447HH425M2510-B](#) [447HH425M2512-B](#) [447HH425NF1110-B](#) [447HH425NF1720-B](#)
[447HJ425M1314-B](#) [447HJ425M1714-B](#) [447HS425M0912-3B-63](#) [447HS425M1114-3B-63](#) [447HS425M1116-5B](#)
[447HS425M1310-4B](#) [447HS425M1312-4B](#) [447HS425M1312-4B-767](#) [447HS425M1314-4B](#) [447HS425M1314-5B](#)
[447HS425M1314-8B](#) [447HS425M1714-5B](#) [447HS425M2516-8B](#) [447HS425M2520-4K](#) [447FS425M1012-4-375](#)
[447HS425M2518-8B](#) [447HH425NF1312-B](#) [447AS425Z171820-4K](#) [447AS425Z172020-4K](#) [447HS425M1310-4B-767](#)
[447HS425M1714-4B](#) [447HS425M2116-4B](#) [447HS425M2314-4-375](#) [447AS425M2832-4](#) [447HS425NF1722-4](#)
[447AS425NF1816-4](#) [447HC659NF1514](#) [447AJ425NF2416](#) [447AJ425NF2822](#) [447AS425NF2422-4](#)
[447AS425NF3632-4](#) [447AS425NF4032-4](#) [447HJ425NF1716](#) [447HS425M1714-4-375](#) [447AS425NF2822-4](#)
[447AJ425NF2420](#)