

REVISION AM

DO NOT
SCALE FROM
THIS PRINT

TABLE 1

LEAD STYLE	TERMINAL	"B"	TUBE (SEE NOTE 9)	PLUG
-01	T-1M6-13-X-2	.230 [5.84]	PT-1-24-01-46	TP-12
-01 (W / PAD OPTION)	T-1M6-13-X-2	.230 [5.84]	PT-1-24-05-29	TP-03
-02	T-1M6-30-X-2	.100 [2.54]	PT-1-24-02-29	TP-24
-02 (W / PAD OPTION)	T-1M6-30-X-2	.100 [2.54]	PT-1-24-05-29	TP-03
-03 (W / PAD OPTION)	T-1M6-04-X-2	.125 [3.18]	PT-1-24-04-09	TP-09
-03 (NO OPTIONS)	T-1M6-04-X-2	.125 [3.18]	PT-1-24-02-29	TP-24
-21	N/A	.230 [5.84]	N/A	N/A
-51	T-1M6-13-X-2	.190 [4.83]	PT-1-24-02-29	TP-24
-52	T-1M6-13-X-2	.205 [5.21]	PT-1-24-10-29	TP-24
-52 (W / PAD OPTION)	T-1M6-13-X-2	.205 [5.21]	PT-1-24-05-29	TP-03
-53	T-1M6-05-X-2	.285 [7.24]	PT-1-24-02-29	TP-24
-54 (6-50 POSITION)	T-1M6-15-X-2	.335 [8.51]	PT-1-24-13-29	TP-24
-54 (5 POSITION)	T-1M6-15-X-2	.335 [8.51]	PT-1-24-10-29	TP-24
-55	T-1M6-16-X-2	.390 [9.91]	PT-1-24-10-29	TP-24
-56	T-1M6-16-X-2	.405 [10.29]	PT-1-24-10-29	TP-24
-57	T-1M6-16-X-2	.430 [10.92]	PT-1-24-03-71	TP-24
-58	N/A	.485 [12.32]	N/A	N/A
-59	N/A	.535 [13.59]	N/A	N/A
-60	N/A	.605 [15.37]	N/A	N/A
-53, -54, -55, -56, -57-60 (W / PAD OPTION)	N/A	N/A	PT-1-24-03-71	TP-09

FTR-1XX-XX-XX-S-XX-X-XX

No OF POSITIONS
-02 THRU -40

LEAD STYLE
SEE TABLE 1

PLATING SPECIFICATION


(VALUES GIVEN ARE IN MICRO-INCHES)
 -G: GOLD, 10 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL
 -T: MATTE TIN CONTACT AND TAIL
 -S: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
 -F: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL (LEAD STYLE SPEC -01 ONLY)
 -SM: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
 -TM: MATTE TIN CONTACT AND TAIL
 -FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL
 -L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL

PACKAGING
(SEE NOTES 10 & 11)
 BLANK: TUBES
 -TR: TAPE & REEL
 (4 POS MIN)
 -FR: FULL REEL QTY TAPE & REEL

PICK & PLACE PAD
 -P: PICK & PLACE PAD
 (USE PPP-11, SEE FIG 2)

OPTION

-XX: -POLARIZING SPECIFICATION
 (XX INDICATES POS TO BE OMITTED)



ROW SPECIFICATION

-S: SINGLE (USE HTMS-50-S)






FIG 1
FTR-1XX-XX-X-S SHOWN

NOTES:

- ⊗ REPRESENTS A CRITICAL DIMENSION.
- MAXIMUM CUT FLASH: .010[0.25]
- MINIMUM PUSHOUT FORCE: 2 LB
- MAXIMUM PIN ROTATION IN BODY: 2°
- MAXIMUM ALLOWABLE BOW AFTER ASSEMBLY: .005[0.13] INCH/INCH
- SHEAR TAILS TO DIMENSION SHOWN.
- MAXIMUM BURR ALLOWANCE: .003[0.08]
- MEASURED AT BEND RADIUS.
- TUBE POSITIONS -05 THRU -50 ONLY FOR THIS LEAD STYLE.
- ORDERS WILL BE PACKAGED ACCORDING TO THE SAMTEC PACKAGING EFFICIENCY STANDARDS (SPES) FOUND ON WWW.SAMTEC.COM
- ATTACH LABEL TO EACH REEL

TABLE 2	
TERMINAL LENGTH	* "L"
-04	.505 [12.83]
-05	.705 [17.91]
-13	.625 [15.88]
-15	.755 [19.18]
-16	.825 [20.96]
* REF FOR OAL PIN LENGTH	

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONS ARE IN INCHES.
 TOLERANCES ARE:
 DECIMALS ANGLES
 .XX: ±.01 [.3]
 .XXX: ±.005 [.13]
 .XXXX: ±.0020 [.051]

MATERIAL: DO NOT SCALE DRAWING
 INSULATOR: LCP, UL 94 VO
 COLOR: BLACK
 TERMINAL: PHOS BRONZE

PROPRIETARY NOTE
 THIS DOCUMENT CONTAINS CONFIDENTIAL AND
 PROPRIETARY INFORMATION AND ALL DESIGN,
 MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
 AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
 INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
 OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
 REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
 OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
 WRITTEN CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
 HI-TEMP TERMINAL MICRO-STRIP (SINGLE ROW)
 DWG. NO.

FTR-1XX-XX-XX-S-XX-X-XX

BY: BRATCHER 07/10/1995 SHEET 1 OF 2

"N" = USE MEASURED DIMENSION
"Q" = { ("N" - .400 [10.16]) / 2 } ±.020[0.51]




FIG 2
-P: PICK AND PLACE PAD
AVAILABLE ON 08 - 40 POSITIONS ONLY

• PROPRIETARY NOTE •
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:
HI-TEMP TERMINAL MICRO-STRIP (SINGLE ROW)

DWG. NO.
FTR-1XX-XX-XX-S-XX-X-XX

BY: BRATCHER 07/10/1995 SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[FTR-108-01-S-S](#) [FTR-108-03-S-S](#) [FTR-140-01-S-S](#) [FTR-103-03-S-S](#) [FTR-106-51-S-S](#) [FTR-102-52-L-S](#) [FTR-103-56-S-S](#) [FTR-115-52-S-S](#) [FTR-104-02-L-S-TR](#) [FTR-109-02-S-S](#) [FTR-109-53-L-S](#) [FTR-115-51-S-S](#) [FTR-116-53-G-S-P](#) [FTR-105-01-S-S](#) [FTR-105-02-L-S-TR](#) [FTR-112-01-S-S](#) [FTR-103-03-L-S](#) [FTR-108-03-S-S-03-P-TR](#) [FTR-135-01-L-S-P-TR](#) [FTR-106-02-G-S](#) [FTR-103-03-G-S](#) [FTR-103-52-L-S](#) [FTR-104-03-G-S](#) [FTR-112-52-G-S](#) [FTR-108-03-S-S-P-TR](#) [FTR-105-01-G-S](#) [FTR-108-03-S-S-02-P-TR](#) [FTR-105-02-L-S](#) [FTR-108-02-S-S-P-TR](#) [FTR-106-01-G-S](#) [FTR-109-53-T-S-P-TR](#) [FTR-104-03-S-S](#) [FTR-108-01-S-S-P-TR](#) [FTR-105-03-G-S](#) [FTR-120-53-S-S-P-TR](#) [FTR-108-52-G-S](#) [FTR-108-52-G-S-P](#) [FTR-108-52-T-S-P](#) [FTR-108-54-G-S](#) [FTR-108-55-G-S](#) [FTR-109-03-S-S](#) [FTR-103-53-S-S](#) [FTR-103-57-T-S](#) [FTR-104-01-T-S](#) [FTR-104-02-S-S](#) [FTR-104-02-T-S](#) [FTR-104-51-S-S](#) [FTR-104-52-S-S](#) [FTR-110-03-S-S](#) [FTR-105-51-G-S](#) [FTR-105-55-T-S](#) [FTR-111-01-S-S](#) [FTR-111-52-T-S](#) [FTR-112-02-S-S](#) [FTR-108-03-S-S-P](#) [FTR-112-52-S-S](#) [FTR-112-53-S-S-P](#) [FTR-112-53-T-S-P](#) [FTR-113-01-T-S](#) [FTR-107-52-G-S](#) [FTR-107-52-S-S](#) [FTR-114-01-S-S](#) [FTR-114-01-S-S-P](#) [FTR-114-01-T-S](#) [FTR-114-02-G-S](#) [FTR-114-02-T-S](#) [FTR-114-03-G-S](#) [FTR-114-03-G-S-P](#) [FTR-114-03-T-S](#) [FTR-114-51-S-S](#) [FTR-114-52-G-S](#) [FTR-110-51-G-S](#) [FTR-110-51-T-S](#) [FTR-110-51-T-S-P](#) [FTR-110-52-G-S-P](#) [FTR-110-52-S-S-P](#) [FTR-110-53-S-S](#) [FTR-110-53-T-S](#) [FTR-110-54-G-S](#) [FTR-110-55-G-S](#) [FTR-110-55-S-S](#) [FTR-113-03-T-S](#) [FTR-114-01-G-S](#) [FTR-116-03-S-S](#) [FTR-112-03-G-S](#) [FTR-112-03-G-S-P](#) [FTR-112-52-G-S-P](#) [FTR-116-55-T-S](#) [FTR-117-01-G-S](#) [FTR-117-52-G-S](#) [FTR-109-53-T-S-P](#) [FTR-110-01-G-S](#) [FTR-110-01-G-S-P](#) [FTR-110-01-S-S](#) [FTR-110-01-S-S-P](#) [FTR-110-01-T-S](#) [FTR-110-02-G-S](#) [FTR-110-02-S-S](#) [FTR-110-02-T-S](#) [FTR-118-52-G-S](#)