


PXP6010/03P/ST/0709 Datasheet

 [View Product Page](#)

Product Name // Flex Cable Connector PXP6010 Series 3
Contact Plug Screw Termination (contacts supplied fitted)
7mm-9mm Cable (Yellow Gland) Plastic Body



// **Product Description:**

- Flex Cable Connectors
- Water and dustproof to IP66, IP68, IP69K when mated with compatible connector
- 30 degree push twist locking, tamperproof lock prevents accidental un-mating
- Plug
- 3 Contacts
- Screw contacts supplied fitted
- Plastic Body
- Cable acceptance 7mm-9mm diameter
- Gland Pack PXP6088 available separately to accomodate all sizes
- PXP6081 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mate with PXP6011 Series Inline, PXP6012 and PXP6014 Series Front Panel Mount Connectors

// **General Information:**

Product Display Title:	Flex Cable Connectors
Product Family:	Circular Power Connectors
Product Series:	6000 Series Buccaneer
Approvals:	UL
Body Colour:	Grey
Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
Body Material Type:	Plastic Body
Contact Type:	Plug Contact
Coupling Type:	Push-Twist
Current Max:	16A, 11A
Diameter Over Coupling Ring Mm:	32mm
Flamability Rating:	UL94V-0
Function:	Flex Cable Connector
Insulation Resistance:	>10 ⁶ MΩ @500V DC
Ip Rating:	IP66, IP68, IP69K
Max Cable Entry Size:	9mm
Min Cable Entry Size:	7mm
Max Contact Accomodation Awg:	14AWG
Min Contact Accomodation Awg:	14AWG
Max Contact Accomodation Mm2:	2.5mm2
Min Contact Accomodation Mm2:	2.5mm2
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	3 Contacts
Rohs Compliant:	Yes
Salt Spray Corrosion Test:	EN60068-2-52 Test Kb Salt Mist (Cyclic) Marine Severity Level 1
Voltage Max:	277V

// **Product PDF Links**

-  [6000 Series power connectors...](#)
-  [6000 Series metal body power...](#)

// **Product 3D CAD Model Links**

-  [PXP6010/03P/ST/07093D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)