



PIN	1	2	3	4	5	6	7	8	9	10
COM0	COM0			3A	1F	1B	2F	2B	3F	3B
COM1		COM1		1A	1E	1G	2E	2G	3E	3G
COM2			COM2	2A	1D	1C	2D	2C	3D	3C

NOTES:

- | | | | |
|-----------------------|------------------------|-----------------------|----------|
| 1. DISPLAY TYPE: | TN | 5. OPERATING VOLTAGE: | 2.7 V |
| 2. VIEWING DIRECTION: | 6:00 | 6. OPERATING TEMP: | -20~70°C |
| 3. POLARIZER MODE: | POSITIVE/TRANSFLECTIVE | 7. STORAGE TEMP: | -30~80°C |
| 4. DRIVER METHOD: | 1/3 DUTY 1/2 BIAS | 8. CONNECTOR: | PIN |