

**BU-P1166-XX-@****(Test Lead: Stackable Banana Plug to Alligator Clip)**

- The BU-P1166 is a stackable, 4mm banana plug to a PVC-jacketed BU-60 alligator clip.
- BU-60 jaw opens to a maximum of 0.31" (7.8mm).
- Uses 18 AWG PVC-jacketed wire.
- Material:

Wire insulation	PVC
Banana overmold	Polypropylene
BU-62 insulator	Flexible PVC
Banana plug	Brass, beryllium copper
BU-60	Nickel-plated steel
- Ratings:

Current	10 Amps
Voltage	Hands-free testing to 1000V
- Length: The "XX" in the model number indicates wire length.  
Available lengths are: 12", 24", 36", 48", 60"
- Color: The "@" in the model number indicates color. Available colors:  
-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS 3 compliant, exemption 6c

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mueller Electric:

[BU-P1166-12-2](#) [BU-P1166-48-2](#) [BU-P1166-60-0](#) [BU-P1166-48-0](#) [BU-P1166-60-2](#) [BU-P1166-24-0](#) [BU-P1166-12-0](#)  
[BU-P1166-36-0](#) [BU-P1166-36-2](#) [BU-P1166-24-2](#)