





Views from "X" rotated



Cable Diameter
7 - 12 mm

Cable Diameter
11 - 17 mm



	Cable Diameter	Solder Contacts	Crimp Contacts	Without Contacts
6 Pole	3 – 7mm	-	-	-
	7 – 12mm	-	-	-
	11 – 17mm	-	KAS6S01-409 1202300067	-
	Crimp range*		0,75-2,5mm²	
7 Pole	3 – 7mm	-	-	-
	7 – 12mm	KAS7S01-555 1202300070	KAS7S01-405 1202300072	-
	11 – 17mm	-	-	-
	Crimp range*		0,75-2,5mm²	
12 Pole	3 – 7mm	-	-	-
	7 – 12mm	KASCS01-555 1202300082	-	-
	11 – 17mm	-	-	-
	Crimp range*		0,34-1,0mm²	
17 Pole	3 – 7mm	-	-	-
	7 – 12mm	-	KASJS01-025 1202300096	-
	11 – 17mm	-	-	-
	Crimp range*		0,34-1,0mm²	
19 Pole (16+3)	3 – 7mm	-	-	-
	7 – 12mm	-	KASLS01-225 1202300102	-
	11 – 17mm	-	-	-
	Crimp range*		0,34-1,0mm²/0,56-1,0mm²	

*Crimp range only applies to "Crimp Contacts" version

Notes:
Tolerances (unless specified): DIN ISO 2768 m

FUNCTIONAL SYMBOLS F A =0 F E =0 F P =0 DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#512581.				molex M23 FA CABLE CONNECTOR FEMALE 90 DEG						
	MM		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
		mm	INCH		EC NO: 753973 DRWN: LIKITV 2023/08/21 CHK'D: ANIKES1 2023/08/30 APPR: GGA 2023/08/31				PRODUCT CUSTOMER DRAWING						
	4 PLACES	± ----	± ----												
	3 PLACES	± ----	± ----												
	2 PLACES	± 0.05	± ----		INITIAL REVISION: DRWN: BBRAUCH 2008/11/12 APPR: JKOLB 2009/03/02				DOCUMENT NUMBER SD-120230-002		DOC TYPE PSD	DOC PART 001	REVISION A		
	1 PLACE	± 0.1	± ----												
	0 PLACES	± ----	± ----												
ANGULAR TOL ± ---- °		THIRD ANGLE PROJECTION				DRAWING A3-SIZE		SERIES 120230		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															