

1604599
<https://www.phoenixcontact.com/us/products/1604599>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



HEAVYCON ADVANCE standard powder-coated sleeve housing B24, with bayonet locking, height 100 mm, with 1x M40 thread, straight cable outlet

Commercial data

Item number	1604599
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF58
Product key	BF7AAA
Catalog page	Page 565 (PC-2011)
GTIN	4017918948276
Weight per piece (including packing)	457.36 g
Weight per piece (excluding packing)	457.36 g
Customs tariff number	85389099
Country of origin	DE

HC-B 24-TMB-100/O1STM40G-STA - Housing



1604599

<https://www.phoenixcontact.com/us/products/1604599>

Technical data


Notes

General	for contact inserts HC-B24, BB46, D64, DD108, HV10/16, M
---------	--

Product properties

Product type	Housing with bayonet locking
Housing type	Sleeve housing
Application	Standard
Type	B24
No. of cable outlets	1
Type of the screw connection	1x M40
Shielded	no
Cable outlet	straight
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57 mm
Height	100 mm
Length	152 mm

Installation dimensions

Width of the assembly cutout	35 mm
Length of the assembly cutout	112 mm

Material specifications

Seal material	NBR
Housing material	Die-cast aluminum
Housing surface material	Powder-coated, gray
Locking latch material	High-grade steel, handle: PA-GF

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

Mechanical properties

HC-B 24-TMB-100/O1STM40G-STA - Housing



1604599

<https://www.phoenixcontact.com/us/products/1604599>

Mechanical data

Type of the screw connection	1x M40
Locking type	Screw

Mounting

Assembly note	In order to guarantee that the protective conductor contact functions even when plugged in at an angle, the two panel-mount flanges must have sufficient electrical contact with the metal mounting panel.
---------------	--

HC-B 24-TMB-100/O1STM40G-STA - Housing


1604599

<https://www.phoenixcontact.com/us/products/1604599>




Drawings

Dimensional drawing



Dimensional drawing

Dimensional drawing



Mounting cutout

1) when M4 screws are used

2) when self-tapping Torx® screws are used (Torx® 20, M4)

HC-B 24-TMB-100/O1STM40G-STA - Housing



1604599

<https://www.phoenixcontact.com/us/products/1604599>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1604599>



EAC
Approval ID: RU C-DE.AI30.B.01102



EAC
Approval ID: RU C-DE.BL08.B.00511

HC-B 24-TMB-100/O1STM40G-STA - Housing



1604599

<https://www.phoenixcontact.com/us/products/1604599>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-B 24-TMB-100/O1STM40G-STA - Housing



1604599

<https://www.phoenixcontact.com/us/products/1604599>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com