







SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal housing: PBT (UL94V-0)
- Item ② Male contact : Copper. Gold plated.
- Item ③ With flange nut: Steel zinc plated.

Electrical:

- Voltage rating: 600 V
- Current rating: 115 A
- Withstanding Voltage: 2.2 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

KU xx C 1 x 1 xxxx G

No. OF POLES
02: 2 POLES
10: 10 POLES

COLOR

- 0: BLACK
- 5: GREEN (RAL 6018/T)
- 6: BLUE
- 8: GREY (RAL 7035/D)

G: Pb<40000ppm
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request.
please contact sales department.

POLE	2	3	4	5	6	7	8	9	10
Dim.E	44.0	59.0	74.0	89.0	104.0	119.0	134.0	149.0	164.0
Dim.L	54.4	69.4	84.4	99.4	114.4	129.4	144.4	159.4	174.4
Dim.P	15.0	30.0	45.0	60.0	75.0	90.0	105.0	120.0	135.0
Tol.	±0.20			±0.35			±0.50		

ANYTEK				CUSTOMER COPY			
TITLE				KU 15.0mm Body Series (Right angle) with flange 2P-10P			
PART NO.				KUXxC1x1xxxxG			
DWG NO.				8KU0003			
APPROVED				CUST NO.			
CHECKED				DESIGNED			
DRAWN				Tolerance			
Runner				UNIT: mm			
2011.04.25				SCALE: NONE			
2010.05.24				SHEET: 01/01			
				REV.: B			
				X. ±0.50			
				X.X ±0.30			
				X.XX ±0.10			
				X° ±1°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[KU02C1510000G](#) [KU03C1510000G](#) [KU04C1510000G](#) [KU05C1510000G](#) [KU06C1510000G](#) [KU07C1510000G](#)
[KU08C1510000G](#) [KU09C1510000G](#) [KU10C1510000G](#)