



General ordering data

Order No.	1970720000
Part designation	SCZ 3.81/04/180FI SN SW
Version	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
EAN	4032248680405
Qty.	50 pc(s).

Similar products

Order No.	Part designation	Version
1970260000	SCZ 3.81/02/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1970700000	SCZ 3.81/02/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1970490000	SCZ 3.81/02/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1970270000	SCZ 3.81/03/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1970710000	SCZ 3.81/03/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1970500000	SCZ 3.81/03/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box

1970310000	SCZ 3.81/04/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1970510000	SCZ 3.81/04/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1970320000	SCZ 3.81/05/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1970740000	SCZ 3.81/05/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1970520000	SCZ 3.81/05/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1970340000	SCZ 3.81/06/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1970760000	SCZ 3.81/06/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1970530000	SCZ 3.81/06/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1970350000	SCZ 3.81/07/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1970770000	SCZ 3.81/07/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1970540000	SCZ 3.81/07/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1970360000	SCZ 3.81/08/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1970780000	SCZ 3.81/08/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1970560000	SCZ 3.81/08/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1970390000	SCZ 3.81/09/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1970790000	SCZ 3.81/09/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1970590000	SCZ 3.81/09/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box

1970410000	SCZ 3.81/10/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1970800000	SCZ 3.81/10/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1970600000	SCZ 3.81/10/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1970420000	SCZ 3.81/11/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1970810000	SCZ 3.81/11/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1970610000	SCZ 3.81/11/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1970430000	SCZ 3.81/12/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1970830000	SCZ 3.81/12/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1970630000	SCZ 3.81/12/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1970450000	SCZ 3.81/13/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1970840000	SCZ 3.81/13/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1970640000	SCZ 3.81/13/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1970460000	SCZ 3.81/14/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1970860000	SCZ 3.81/14/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1970660000	SCZ 3.81/14/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1970470000	SCZ 3.81/15/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1970870000	SCZ 3.81/15/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box

1970670000	SCZ 3.81/15/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1970480000	SCZ 3.81/16/180FI SN OR	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1970880000	SCZ 3.81/16/180FI SN SW	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1970680000	SCZ 3.81/16/180FI SN GN	PCB plug-in connector, Male connectors, Clamping yoke connection, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box