

233-100-H8 Weld mount hermetic receptacle


MIL-DTL-38999 Series III type

How To Order Commercial						
Sample Part Number	233-100	-H8	Z1	11-35	P	N
Series / Basic Part No.	Series 23 SuperNine® Hermetic Receptacle					
Connector Style	H8 = Weld Mount					
Finish*	Z1 = CRES, Passivated ZL = CRES, Nickel Finish					
Shell Size - Insert Arrangement*	Per MIL-STD-1560					
Contact Type	P = Pin, Solder Cup S = Socket, Solder Cup X = Pin, Eyelet Z = Socket, Eyelet C = Pin, PCB D = Socket, PCB					
Alternate Key Position*	A, B, C, D, E, N = Normal					

***Refer to Section A for complete details**

Modification codes may be added directly to the end of any valid part number

Dimensions					
Shell Size Code	Shell Size	A Thread	Ø B	Ø C	Ø D
A	9/09	.6250-1P-.3L-TS-2A	.941 (23.9) .929 (23.6)	.984 (25.0) .972 (24.7)	.134 (3.4) .118 (3.0)
B	11	.7500-1P-.3L-TS-2A	1.063 (27.0) 1.051 (27.0)	1.106 (28.1) 1.094 (27.8)	.134 (3.4) .118 (3.0)
C	13	.8750-1P-.3L-TS-2A	1.189 (30.2) 1.177 (28.9)	1.232 (31.3) 1.220 (31.0)	.134 (3.4) .118 (3.0)
D	15	1.0000-1P-.3L-TS-2A	1.315 (33.4) 1.303 (33.1)	1.358 (34.5) 1.346 (34.2)	.134 (3.4) .118 (3.0)
E	17	1.1875-1P-.3L-TS-2A	1.402 (35.6) 1.390 (35.3)	1.445 (36.7) 1.433 (36.4)	.134 (3.4) .118 (3.0)
F	19	1.2500-1P-.3L-TS-2A	1.547 (39.3) 1.535 (39.0)	1.591 (40.4) 1.579 (40.1)	.134 (3.4) .118 (3.0)
G	21	1.3750-1P-.3L-TS-2A	1.689 (42.9) 1.677 (42.6)	1.732 (44.0) 1.720 (43.7)	.134 (3.4) .118 (3.0)
H	23	1.5000-1P-.3L-TS-2A	1.854 (47.1) 1.842 (46.8)	1.898 (48.2) 1.886 (47.4)	.165 (4.2) .149 (3.8)
J	25	1.6250-1P-.3L-TS-2A	1.941 (49.3) 1.929 (49.0)	1.984 (50.4) 1.972 (50.1)	.165 (4.2) .149 (3.8)

Contact Size & Dia.	
PRINTED CIRCUIT TAIL CONFIGURATIONS CONTACT STYLE C AND D 	
Contact Size	Ø P
22D	.011 (0.28) .015 (0.38)
20	.024 (0.61) .028 (0.71)
16	.0635 (1.61) .0615 (1.56)
12	.095 (2.41) .093 (2.36)

Hermetic Leak Rate Mod Codes	
Designator	Required Leak Rate
-585A	1 x 10 ⁻¹⁰ cc Helium per second
-585B	1 x 10 ⁻⁹ cc Helium per second
-585C	1 x 10 ⁻⁸ cc Helium per second

Wire Accommodation	
Contact Size	Wire Gauge
22D	#22 - #28
20	#20 - #24
16	#16 - #20
12	#12 - #14




How To Order MS						
Sample Part Number	D38999	/27	Y	B-35	P	N
Series / Basic Part No.	MIL-DTL-D38999 Series III Type					
Connector Style	/27 = Weld Mount					
Finish*	Y = CRES, Passivated N = CRES, Nickel Finish					
Shell Size - Insert Arrangement*	Per MIL-STD-1560					
Contact Type	P = Pin, Solder Cup S = Socket, Solder Cup X = Pin, Eyelet Z = Socket, Eyelet C = Pin, PCB Flex Feedthru D = Socket, PCB Flex Feedthru					
Alternate Key Position*	A, B, C, D, E, N = Normal					

***Refer to Section A for complete details**

Modification codes may be added directly to the end of any valid part number

D



Mates With	
Plug Part Number	Description
233-105SG6	SuperNine® plug with single integrated band porch
233-105BG6	SuperNine® plug with integrated band porch and boot groove
233-105DG6	SuperNine® plug with double integrated band porch
233-105-G6	SuperNine® plug with accessory attachment threads

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[233-100-H8Z109-35PA](#) [233-100-H8Z109-35PC](#) [233-100-H8Z109-35PN](#) [233-100-H8Z109-98PN](#) [233-100-H8Z111-05PN](#) [233-100-H8Z111-35PA](#) [233-100-H8Z111-35PB](#) [233-100-H8Z111-35PC](#) [233-100-H8Z111-35PD](#) [233-100-H8Z111-35PE](#) [233-100-H8Z111-35PN](#) [233-100-H8Z111-98PA](#) [233-100-H8Z111-98PB](#) [233-100-H8Z111-98PN](#) [233-100-H8Z113-04PN](#) [233-100-H8Z113-08PN](#) [233-100-H8Z113-98PA](#) [233-100-H8Z113-98PB](#) [233-100-H8Z113-98PD](#) [233-100-H8Z113-98PN](#) [233-100-H8Z115-35CA](#) [233-100-H8Z115-35PN](#) [233-100-H8ZL11-05PA](#) [233-100-H8ZL11-05PN](#) [233-100-H8ZL11-35PN](#) [233-100-H8ZL11-98PA](#) [233-100-H8ZL11-98PN](#) [233-100-H8ZL13-08PN](#) [233-100-H8ZL13-35PN](#) [233-100-H8ZL15-35PN](#) [233-100-H8Z109-35SN](#) [233-100-H8ZL17-26XN](#) [233-100-H8Z109-35PB](#) [233-100-H8ZL19-11SN](#) [233-100-H8ZL19-35PN](#) [233-100-H8Z115-05PN](#) [233-100-H8Z121-35SN](#) [233-100-H8ZL19-11SA](#) [233-100-H8Z111-35CB](#) [233-100-H8Z117-35SN](#) [233-100-H8Z111-02CN](#) [233-100-H8Z109-35XN](#) [233-100-H8Z109-98CN](#) [233-100-H8Z111-04XN](#) [233-100-H8Z109-35CN](#) [233-100-H8ZL21-11SN](#) [233-100-H8Z111-02PN](#) [233-100-H8ZL17-06SN](#) [233-100-H8Z111-35CN](#) [233-100-H8Z115-97PA](#) [233-100-H8Z115-97PN](#) [233-100-H8Z109-35XB](#) [233-100-H8Z109-35XA](#)