



General ordering data

Order No.	1962610000
Part designation	SAISW-5/7-(KV)
Version	Sensor/Actuator plug-in connector, M12, pin, 90°, screw
EAN	4032248644742
Qty.	1 pc(s).

Technical data

Ambient temperature, max.	85 °C
Ambient temperature, min.	-40 °C
Bus line connection via	screw
Cable connection diameter	4...6 mm (PG7)/ 6...8 mm (PG9)
Cable gland	PG 7
Connection cross-section	0.25...0.75 mm ²
Connection cross-section, max.	0.75 mm ²
Connection cross-section, min.	0.25 mm ²
Contact surface	CuSnZn
Contact tube diameter	M12
Housing material	PBT
Plugging cycles	500
Pollution severity	3
Protection class	IP 67
Rated current	4 A
No. of poles	5
Version	pin, 90°

Classifications

ETIM 2.0	EC000516
ETIM 3.0	EC002062
eClass 4.1	27-26-07-01
eClass 5.0	27-26-07-01
eClass 5.1	27-26-07-01

Similar products

Order No.	Part designation	Version
1807370000	SAISW- 5/9	Sensor/Actuator plug-in connector, M12, pin, 90°, screw
9457290000	SAISW-4/7	Sensor/Actuator plug-in connector, M12, pin, 90°, screw
1962620000	SAISW-4/7-(KV)	Sensor/Actuator plug-in connector, M12, pin, 90°, screw
1807360000	SAISW-4/9	Sensor/Actuator plug-in connector, M12, pin, 90°, screw
9456950000	SAISW-5/7	Sensor/Actuator plug-in connector, M12, pin, 90°, screw