





REV.	ECN NO.	DATE	SIGN	DESCRIPTION


ALTW
CONFIDENTIAL
2014-09-12
R&D DEPT.




ALTW
DCC. DEPT.
CONFIDENTIAL
2014.11.26
ISSUED



- Note:
- * $\varnothing$ Important Dimension To Check.
 - * Waterproof Rate: IP68
 - * Working Voltage Rating: AC 300 V
 - * Working Current Rating: 10A
 - * Flame Class: UL94V-0 (UV Resistance)
 - * Housing: Nylon+GF, Black
 - * Female Pin: Copper Alloy, Gold Plated
 - * Nut: Nylon+GF, Black
 - * Gasket: Silicone, Gary
 - * Use Whitout Waterproof Cap
Panel Thickness Max: 4.0mm
 - * Use Whit Waterproof Cap
Panel Thickness Max: 3.0mm



Pin Assignments
Front View



Recommended Panel Cut-out

UNIT:mm				TITLE X Lok B-Size Receptacle Front Fastened M Conn F 3 Pin				Amphenol LTW				ITEM NO BB-03PMFS-QC8001		DRAWN BY Micky		DATE 2014-09-12			
TOLERANCE .X ±0.25				SCALE 2:1				SIZE A4		SHEET 1 OF 1		DWG NO BB-03PMFS-QC8001				CHECKED BY Spring		DATE 2014-09-12	
				REV. A		WC-REV. A.2		QC: Inspection item				CUSTOMER ALTW		APPROVED BY Kevin		DATE 2014-09-12			
1		2		3		4		5		6		7		8		FMM10702-01-02A1			
安費諾亮泰企業股份有限公司																			