





Conn.2
Female Conn
Female Pin



Conn.1
Female Conn
Female Pin



Conn.3
Male Conn
Male Pin



- △ Note:
- * RoHS Compliant
 - * ∅ Important dimension
 - * C1 & C2
 - △ Waterproof rate: IP68, mated 1m/24h
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Gray
 - Nut: Thermoplastic, Black
 - * C3
 - △ Waterproof rate: IP68, mated 1m/24h
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - * Wire: UL1007, 16AWG
 - * Wire: UL1015, 14AWG
 - * Outer Mold: Thermoplastic, Black

UNIT:mm		TITLE	
TOLERANCE		ACC, XLOK, C-20A, T ADA W/O CB	
±0.5mm		FFM, PUSH LOCK	
SCALE	SIZE	SHEET	OF
1:1	A4	1	2
REV.	WC-REV.	QC: Inspection item	
C	.0		

Amphenol LTW
安費諾亮泰企業股份有限公司


ITEM NO		DRAWN BY		DATE	
		Eric		2021/11/24	
DWG NO		CHECKED BY		DATE	
AB-CC-XXXXXX-FFM-TQ001		Wen		2021/11/24	
CUSTOMER		APPROVED BY		DATE	
ALTW		Neo		2021/11/24	

AB-CC-XXXXXX-FFM-TQ001



XXXXXX: No. Of Pin

Connection Diagram



Pin Assignments Front View

	Pin Assignments Front View	
	2 Pin	3 Pin
Male		
Female		
Pin Out	Pin# Color	Pin# Color
	Pin1 White 白 Pin3 Black 黑	Pin1 White 白 Pin2 Green 綠 Pin3 Black 黑

UNIT:mm



TOLERANCE

±0.5mm

TITLE ACC, XLOK, C-20A, T ADA W/O CB
FFM, PUSH LOCK

SCALE 1:1

SIZE A4

SHEET 2 OF 2

REV. C

WC-REV. .0

QC: Inspection item

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO

DWG NO

AB-CC-XXXXXX-FFM-TQ001

CUSTOMER

ALTW

DRAWN BY

Eric

CHECKED BY

Wen

APPROVED BY

Neo

DATE

2011/11/24

DATE

2011/11/24

DATE

2011/11/24