







REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2016-05-19	Wes	Change Rev.01 To Rev.A




White Printing



Pin Assignments
Front View



Recommended Panel
Cut-Out



Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP68(Unmated)
In 1 meters water within 24hours.
- * Working Voltage Rating: AC 300V
- * Working Current: 20A
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Liquid Glue: Black
- * Nut: Nylon+GF, Black
- * Gasket: Silicone, Gray
- * Panel Thickness Max: 3.6mm

UNIT:mm	TITLE			ITEM NO		DRAWN BY		DATE
	X-Lok D Size 20A(For Power) Receptacle Rear 3P M Conn M Pin			DC-03RMMS-QC800P		Wes Fan		2016-05-19
				DC-03RMMS-QC800P		Spring Liu		2016-05-19
				ALTW		Kevin Hu		2016-05-19
TOLERANCE		SCALE	SIZE	SHEET	OF	DATE		
.X ±0.25		3:2	A4	1	1	2016-05-19		
.XX ±0.1		REV.	WC-REV.	QC: Inspection item		2016-05-19		
.XXX ±0.05		A	A.2					
ANGLES ±1°								

Amphenol LTW
安費諾亮泰企業股份有限公司