








5	6	7	8
REV.	ECN NO.	DATE	SIGN



Pin Assignments
Front View



Recommended
Panel Cut-Out



Note:

- * @C Important Dimension To Check.
- * Waterproof Rate: IP67
- * Connector: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Nut: Nylon+GF, Black
- * Gasket: Silicon, Gray
- * Maximum Panel Thickness: 4.5mm
- * UL94V-0 Materials used
- * All Parts Are RoHS Compliant
- * For UL2238 Certificated E318730

UNIT:mm		TITLE Power, Panel Lock 4Pin M Conn. M Pin 20Amps+2Amps
TOLERANCE		SCALE Free SHEET 1 OF 1
.X ±0.25		REV. A SIZE A4 @C :Inspection Item
.XX ±0.1		
.XXX ±0.05		
ANGLES ±1°		

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO PWCU-04RMMS-LC7002	DRAWN BY Ivan Lin	DATE 2010/01/28
DWG NO PWCU-04RMMS-LC7002	CHECKED BY Aric	DATE 2010/01/29
CUSTOMER ALTW	APPROVED BY Max	DATE 2010/01/29