

# Han 6HP-PFT housing-black



Image is for illustration purposes only. Please refer to product description.

Part number	19 39 006 1111
Specification	Han 6HP-PFT housing-black

## Identification

Category	Hoods/Housings
Series of hoods/housings	Han® HP
Type of hood/housing	Panel feed through housing
Description of hood/housing	EMC version

## Version

Size	6 B
Version	Top entry
Cable entry	1x M25
Locking type	Screw locking
Field of application	Hoods/housings for rough environments

## Technical characteristics

Tightening torque (screw locking)	3 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)



**Pushing Performance**  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	344 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140832459
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors