

SPECIFICATIONS:

MATERIALS:

HOUSING:

PBT, UL94 V-0, BLACK

CONTACTS:

GOLD PLATED BRASS

(SEE P/N KEY BELOW)

NUT:

NICKEL PLATED BRASS

ORING:

EPDM, BLACK

ELECTRICAL:

RATED CURRENT:

4A

RATED VOLTAGE:

250V

INSULATION RESISTANCE:

100 MOhms MIN.

CONTACT RESISTANCE:

10 mOhms MAX.

ENVIRONMENT:




OPERATING TEMPERATURE: -40°C TO +85°C

WATER PROOF:

IP67

MAX WIRE AWG:

20



NORCOMP MATING PART NUMBERS:

858-L03-203RKT4*

858-R03-203RSS4*

858-R03-203RSU4*

859-L03-203R004*

860-003-213R004*

861-L03-213R004*

*Also all material and contact plating variants

858-R03-103RLUY

3 = BRASS/NICKEL NUT
S = STAINLESS STEEL NUT1 = GOLD FLASH
4 = 10 μ " GOLD

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03/07/2016

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	NTS	1	REV
SHEET	1	1	6
DWG NO.	858-R03-103RLUY		