

HC-STA-B10-HHFD-1TTP21-EL-AL - Housing



1412598

<https://www.phoenixcontact.com/us/products/1412598>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B10, for double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x Pg21, height: 72 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412598
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 610 (C-2-2019)
GTIN	4055626059259
Weight per piece (including packing)	185.6 g
Weight per piece (excluding packing)	185.6 g
Customs tariff number	85389099
Country of origin	PL

HC-STA-B10-HHFD-1TTP21-EL-AL - Housing



1412598

<https://www.phoenixcontact.com/us/products/1412598>

Technical data

Notes

General	for contact inserts HC-B10, BB18, DD42, M, K8/24, HV03
General	also available as a powder-coated or color version: 1372663 HC-STA-B10-HHFD-1TTP21-EL/...


Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B10
No. of cable outlets	1
Type of the screw connection	1x Pg21
Type	Tall design
Cable outlet	straight
Pg screw connection	none

Data management status

Article revision	02
------------------	----

Dimensions

Dimensional drawing	
Width	44 mm
Height	72 mm
Length	73 mm

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	1x Pg21
Locking type	Pin

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
----------------------	------

HC-STA-B10-HHFD-1TTP21-EL-AL - Housing



1412598

<https://www.phoenixcontact.com/us/products/1412598>

	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B10-HHFD-1TTP21-EL-AL - Housing


1412598

<https://www.phoenixcontact.com/us/products/1412598>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B10-HHFD-1TTP21-EL-AL - Housing



1412598

<https://www.phoenixcontact.com/us/products/1412598>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412598>



DNV
Approval ID: TAE000037S



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026



EAC
Approval ID: RU C-DE.AI30.B.01102



EAC
Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

HC-STA-B10-HHFD-1TTP21-EL-AL - Housing



1412598

<https://www.phoenixcontact.com/us/products/1412598>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com