

HC-STA-B24-HLFD-1TTP29-EL-AL - Housing



1412782

<https://www.phoenixcontact.com/us/products/1412782>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing B24, for double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 1, straight, 1x Pg29, height: 60 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412782
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF56
Product key	BF7APB
Catalog page	Page 638 (C-2-2019)
GTIN	4055626060484
Weight per piece (including packing)	233.8 g
Weight per piece (excluding packing)	229.4 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B24-HLFD-1TTP29-EL-AL - Housing



1412782

<https://www.phoenixcontact.com/us/products/1412782>

Technical data

Notes

General	for contact inserts HC-B24, BB46, D64, DD108, HV10/16, M
General	also available as a powder-coated or color version: 1373258 HC-STA-B24-HLFD-1TTP29-EL/...


Product properties

Product type	Housing with locking latch
Housing type	Sleeve housing
Application	Standard
Type	B24
No. of cable outlets	1
Type of the screw connection	1x Pg29
Type	Low design
Cable outlet	straight
Pg screw connection	none

Data management status

Article revision	03
------------------	----

Dimensions

Dimensional drawing	
Width	44 mm
Height	60 mm
Length	120 mm

Internal dimensions

Length of internal thread	14 mm
---------------------------	-------

Material specifications

Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated

Mechanical properties

Mechanical data

Type of the screw connection	1x Pg29
Locking type	Pin

Environmental and real-life conditions

HC-STA-B24-HLFD-1TTP29-EL-AL - Housing



1412782

<https://www.phoenixcontact.com/us/products/1412782>

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B24-HLFD-1TTP29-EL-AL - Housing


1412782

<https://www.phoenixcontact.com/us/products/1412782>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B24-HLFD-1TTP29-EL-AL - Housing



1412782

<https://www.phoenixcontact.com/us/products/1412782>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1412782>

**DNV**
Approval ID: TAE000037S

**cUL Recognized**
Approval ID: E255026

**UL Recognized**
Approval ID: E255026

**EAC**
Approval ID: RU C-DE.AI30.B.01102

**EAC**
Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

HC-STA-B24-HLFD-1TTP29-EL-AL - Housing



1412782

<https://www.phoenixcontact.com/us/products/1412782>

Classifications

ECLASS

ECLASS-11.0	27440202
ECLASS-12.0	27440202
ECLASS-13.0	27440202

ETIM

ETIM 9.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%