





Pin headers SLS 5.08



Pin headers SLS 5.08B



Technical Data		VDE	UL	CSA
Rated voltage	V	250*	300	300
Rated current	A	12	10	10
Clamping range max.	mm ² /AWG	2.5	12	12

*Overvoltage category III / Pollution severity 3

Additional technical data see page 223

Technical Data		VDE	UL	CSA
Rated voltage	V	250*	300	300
Rated current	A	12	10	10
Clamping range max.	mm ² /AWG	2.5	12	12

*Overvoltage category III / Pollution severity 3

Additional technical data see page 223

Colour

Poles	Type	Cat. No.	Cat. No.	Qty.
2	SLS 5.08/2	1627090000	1644920000	100
3	SLS 5.08/3	1627100000	1644930000	100
4	SLS 5.08/4	1627110000	1644940000	100
5	SLS 5.08/5	1627120000	1644950000	50
6	SLS 5.08/6	1627130000	1644960000	50
7	SLS 5.08/7	1627140000	1644970000	50
8	SLS 5.08/8	1627150000	1644980000	50
9	SLS 5.08/9	1627160000	1644990000	50
10	SLS 5.08/10	1627170000	1645000000	50
11	SLS 5.08/11	1627180000	1645010000	50
12	SLS 5.08/12	1627190000	1645020000	50
13	SLS 5.08/13	1627200000	1645030000	50
14	SLS 5.08/14	1627210000	1645040000	50
15	SLS 5.08/15	1627220000	1645050000	50
16	SLS 5.08/16	1627230000	1645060000	50
17	SLS 5.08/17	1644840000	1645070000	20
18	SLS 5.08/18	1644850000	1645080000	20
19	SLS 5.08/19	1644860000	1645090000	20
20	SLS 5.08/20	1644870000	1645100000	20
21	SLS 5.08/21	1644880000	1645110000	20
22	SLS 5.08/22	1644890000	1645120000	20
23	SLS 5.08/23	1644900000	1645130000	20
24	SLS 5.08/24	1644910000	1645140000	20

Colour

Poles	Type	Cat. No.	Cat. No.	Qty.
2	SLS 5.08/2B	1627240000	1645230000	100
3	SLS 5.08/3B	1627250000	1645240000	100
4	SLS 5.08/4B	1627260000	1645250000	100
5	SLS 5.08/5B	1627270000	1645260000	50
6	SLS 5.08/6B	1627280000	1645270000	50
7	SLS 5.08/7B	1627290000	1645280000	50
8	SLS 5.08/8B	1627300000	1645290000	50
9	SLS 5.08/9B	1627310000	1645300000	50
10	SLS 5.08/10B	1627320000	1645310000	50
11	SLS 5.08/11B	1627330000	1645320000	50
12	SLS 5.08/12B	1627340000	1645330000	50
13	SLS 5.08/13B	1627350000	1645340000	50
14	SLS 5.08/14B	1627360000	1645350000	50
15	SLS 5.08/15B	1627370000	1645360000	50
16	SLS 5.08/16B	1627380000	1645370000	50
17	SLS 5.08/17B	1645150000	1645380000	20
18	SLS 5.08/18B	1645160000	1645390000	20
19	SLS 5.08/19B	1645170000	1645400000	20
20	SLS 5.08/20B	1645180000	1645410000	20
21	SLS 5.08/21B	1645190000	1645420000	20
22	SLS 5.08/22B	1645200000	1645430000	20
23	SLS 5.08/23B	1645210000	1645440000	20
24	SLS 5.08/24B	1645220000	1645450000	20

Accessories	Page
Fixing	-
Marking	196
Coding	198, 199
Miscellaneous	201-207

Accessories	Page
Fixing	193
Marking	196
Coding	198, 199
Miscellaneous	201-207