

# CT3753

## Banana Plug Test Lead

UL Listed 4mm Straight Banana Plug to Right-Angle Banana Plug...

### Description

UL Listed 4mm Straight Sheathed Banana Plug to Right-Angle Sheathed Banana Plug Test Lead. Highly flexible silicone jacketed test lead wire.

- Banana Contact: BeCu, Nickel Plt.
- Available in 2 standard lengths



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

# Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### **Specifications**

<b>UL Rating</b>	1,000 V CAT III
<b>Current, Max</b>	10 A
<b>Jacket Material</b>	Silicone
<b>Conductor Area</b>	0.87 mm <sup>2</sup>
<b>Wire Gauge, AWG</b>	18 AWG
<b>Stranding (# x dia.)</b>	168 x 0.07 mm
<b>Jacket OD</b>	3.7 mm (0.146")
<b>Temperature (degrees)</b>	-20 to +80C
<b>RoHS (2011/65/EU)</b>	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT3753-150-0](#) [CT3753-200-2](#) [CT3753-100-2](#) [CT3753-200-0](#) [CT3753-100-0](#) [CT3753-150-2](#)