



**Part Number :** 936011051

**Product Description :** GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, Size «32x13», Black

**Series Number :** 93601

**Status :** Active

**Product Category :** Heavy-Duty Connectors

**Engineering Number :** 7808.6669.1



## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
--------	--------

Category	Heavy-Duty Connectors
Series	93601
Description	GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Side Entry, Size «32x13», Black
Component Type	Single Lever Bulkhead Housing
IP Rating	IP66, IP67
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191867984

## Agency

CSA	256883
UL	E249674

## Electrical

Voltage - Maximum	500V
-------------------	------

## Physical

Component Size	«32X13»
Entry Location	Side
Flammability	UL 94V-0
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Polyamide
Material - Lever	Polyamide
Mounting Style	Bulkhead
Net Weight	32.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	N/A
Thread Type	N/A

---

## Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts

---

---

This document was generated on Oct 14, 2024