





APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max.
Contact resistance: 20 mohms max.
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC/DC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/25/05	
A		REDRAWN	8/3/12	
B		REVISED DIM.	06/13/13	
C		UPDATE DRAWING	9/10/15	AV/RT

Positions: 04 thru 100
A = .050 [1,27] x No. of Positions per Row +.016 [0,40]
B = .050 [1,27] x No. of Spoces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØXX	± .10	TITLE .050 x .100 DUAL ROW RECEPTACLE STRIP LOW PROFILE			
.XX	± .020	ØXXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN				SS			
CHECKED				5/25/05			
APPROVED				X			
SIZE				PART NO.			
REF:				HRS-2B-XX-GA			
SCALE: NTS				SHEET 1 OF 1			
REV.				C			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HRS-2B-18-GA](#) [HRS-2B-14-GA](#) [HRS-2B-12-GA](#) [HRS-2B-16-GA](#) [HRS-2B-20-GA](#) [HRS-2B-04-GA](#) [HRS-2B-08-GA](#)
[HRS-2B-06-GA](#) [HRS-2B-10-GA](#)