







SECTION A-A




9-2399606-3	D	M	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	M	PA66-GF	AQUA RED	(245)	1	7
9-2399606-2	D	L	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	L	PA66-GF	AQUA BROWN	(245)	1	7
9-2399606-1	D	K	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	K	PA66-GF	AQUA GREEN	(245)	1	7
8-2399606-9	D	J	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	J	PA66-GF	ORANGE	(245)	1	7
8-2399606-8	D	H	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	H	PA66-GF	YELLOW	(245)	1	7
8-2399606-7	D	G	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	G	PA66-GF	RED	(245)	1	7
8-2399606-6	D	F	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	F	PA66-GF	BROWN	(245)	1	7
8-2399606-5	D	E	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	E	PA66-GF	GREEN	(245)	1	7
8-2399606-4	D	D	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	D	PA66-GF	PURPLE	(245)	1	7
8-2399606-3	D	C	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	C	PA66-GF	BLUE	(245)	1	7
8-2399606-2	D	B	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	B	PA66-GF	NATURE	(245)	1	7
8-2399606-1	D	A	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING FOLLOW 8-2399606-1	A	PA66-GF	BLACK	(245)	1	7
TE-ASSY-NO	TE REV.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR /TREATMENT	WEIGHT (g)	QTY	ITEM
				CODE HOUSING	A	PA66-GF	BLACK	1	7	
				HWIL WIRE(LEONI) MOCAR 180 E 0.550MM,WHITE	-	-	-	2	6	
				FACE SEAL	-	SILICONE	RED	1	5	
				BUSBAR, TOP SIDE	-	-	-	1	4	
				HEADER TPA	-	PA66-GF	RED	1	3	
				FINGER PROTECTION CAP	-	PA66-GF	BLACK	1	2	
				HEADER HOUSING 180DEG,1POS	-	AL-ALLOY	PASSIVATION	1	1	





SECTION A-A

1. MISSING DIMENSIONS ACC. TO 8-2399606-1



SECTION B-B


1. MISSING DIMENSIONS ACC. TO 8-2399606-1

5-2399606-3	D	M	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
5-2399606-2	D	L	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	L	PA66-GF	AQUA BROWN	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
5-2399606-1	D	K	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	K	PA66-GF	AQUA GREEN	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-9	D	J	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	J	PA66-GF	ORANGE	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-8	D	H	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	H	PA66-GF	YELLOW	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-7	D	G	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	G	PA66-GF	RED	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-6	D	F	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	F	PA66-GF	BROWN	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-5	D	E	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	E	PA66-GF	GREEN	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-4	D	D	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	D	PA66-GF	PURPLE	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-3	D	C	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	C	PA66-GF	BLUE	245	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-2	D	B	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	B	PA66-GF	NATURE	(245)	1	7
				FOLLOW 4-2399606-1	-	-	-		-	1-6
4-2399606-1	D	A	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	A	PA66-GF	BLACK	(245)	1	7
				HVIL WIRE(LEONI MOCAR 180 E 0.5SQMM,WHITE ACCORDING TO LV112) WITH TERMINAL	-	-	-		2	6
				FACE SEAL	-	SILICONE	RED		1	5
				BUSBAR, BACK SIDE	-	-	-		1	4
				HEADER TPA	-	PA66-GF	RED		1	3
				FINGER PROTECTION CAP	-	PA66-GF	BLACK		1	2
				HEADER HOUSING 180DEG,1POS	-	AL-ALLOY	PASSIVATION		1	1
TE-ASSY-NO	TE REV.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR /TREATMENT	WEIGHT (g)	QTY	ITEM


7-2399606-3	D	M	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
7-2399606-2	D	L	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	L	PA66-GF	AQUA BROWN	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
7-2399606-1	D	K	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	K	PA66-GF	AQUA GREEN	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-9	D	J	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	J	PA66-GF	ORANGE	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-8	D	H	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	H	PA66-GF	YELLOW	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-7	D	G	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	G	PA66-GF	RED	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-6	D	F	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	F	PA66-GF	BROWN	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-5	D	E	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	E	PA66-GF	GREEN	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-4	D	D	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	D	PA66-GF	PURPLE	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-3	D	C	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	C	PA66-GF	BLUE	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-2	D	B	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	B	PA66-GF	NATURE	(245)	1	7
				FOLLOW 6-2399606-1	-	-	-		-	1-6
6-2399606-1	D	A	1POS,PIN DIA 14.0 HDR ASSY,180DEG	CODE HOUSING	A	PA66-GF	BLACK	(245)	1	7
				HVIL WIRE(LEONI MOCAR 180 E 0.5SQMM,WHITE ACCORDING TO LV112) WITH TERMINAL	-	-	-		2	6
				FACE SEAL	-	SILICONE	RED		1	5
				BUSBAR, LEFT SIDE	-	-	-		1	4
				HEADER TPA	-	PA66-GF	RED		1	3
				FINGER PROTECTION CAP	-	PA66-GF	BLACK		1	2
				HEADER HOUSING 180DEG,1POS	-	AL-ALLOY	PASSIVATION		1	1
TE-ASSY-NO	TE REV.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR /TREATMENT	WEIGHT (g)	QTY	ITEM

REVISIONS				
P	LTN	DESCRIPTION	DATE	APPD
-	-	SEE SHEET 1	-	-

2



THIS DRAWING IS A CONTROLLED DOCUMENT.				DESIGNED BY: S. TAN	29DEC2021
DIMENSIONS: (mm)				CHECKED BY: J. L. L.	29DEC2021
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APPROVED BY: J. L. L.	29DEC2021
±0.5				PRODUCT SPEC	1408-160407
±0.1				APPLICATION SPEC	114-160222
±0.001				WEIGHT	SEE TABLE
±0.0001				CUSTOMER DRAWING	SCALE 2:1
FINISH SPEC				DATE	29DEC2021
MATERIAL				SIZE	1408-160407
SEE TABLE				CASE CODE	00779
DRAWING NO				DRAWING NO	2399606
RESTRICTED TO				REV	0



2:1	SHEET 5 OF 5	REV 0
-----	--------------	-------