

RC-12S1N129006 - Coupler connector

1598678

<https://www.phoenixcontact.com/us/products/1598678>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Socket, Solder cup, cable diameter range: 7.5 mm ... 9.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1241004

Commercial data

Item number	1598678
Packing unit	20 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAFG
GTIN	4046356222020
Weight per piece (including packing)	76.95 g
Weight per piece (excluding packing)	69.4 g
Customs tariff number	85366990
Country of origin	DE

RC-12S1N129006 - Coupler connector

1598678

<https://www.phoenixcontact.com/us/products/1598678>



Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Contact diameter Power contacts	1 mm
Litz wire cross-section Power contacts min.	0.08 mm ²
Litz wire cross-section Power contacts max.	1 mm ²
Rated current Power contacts	8 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overtoltage category	III
Degree of pollution	3

Housing

Housing material	Metal
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	7.5 mm ... 9.5 mm
-------------------------	-------------------

RC-12S1N129006 - Coupler connector


1598678

<https://www.phoenixcontact.com/us/products/1598678>



Drawings

Schematic diagram



Connector pin assignment

RC-12S1N129006 - Coupler connector

1598678

<https://www.phoenixcontact.com/us/products/1598678>



Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-12S1N129006 - Coupler connector

1598678

<https://www.phoenixcontact.com/us/products/1598678>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	889b1557-d811-428c-96bd-185e8f86ad3a

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com