

	I0		9		8		7		6		5		4		3		2		I	
F	MATERIAL NUMBER	ALTERNATE NUMBER	WIRE SIZE AWG	INSULATION COLOR	CONNECTOR ID	MAX. WIRE INSUL. DIA.		LENTH "L2"	TAPE HEIGHT "T"	DESCRIPTION										
						STANDARD END	FUNNEL END													
	I920200I0	AS-932	22-I8	LIGHT RED	.06I	.I6I	.I47	I.07	----	LOOSE PIECE										
	I920200II	AS-932-DK	22-I8	DARK RED	.06I	.I6I	.I47	I.07	----	LOOSE PIECE										
	I920200I2	AS-932-DKT	22-I8	DARK RED	.06I	.I6I	.I47	I.07	.480	TAPE MOUNTED										
E	I92020026	BS-942	I6-I4	LIGHT BLUE	.087	.I99	.I85	I.07	----	LOOSE PIECE										
	I92020030	BS-942T	I6-I4	LIGHT BLUE	.087	.I99	.I85	I.07	.480	TAPE MOUNTED										
	I92020027	BS-942-DK	I6-I4	DARK BLUE	.087	.I99	.I85	I.07	----	LOOSE PIECE										
	I92020029	BS-942-DKT	I6-I4	DARK BLUE	.087	.I99	.I85	I.07	.480	TAPE MOUNTED										
	I92020028	BS-942-DKBT	I6-I4	DARK BLUE	.087	.I99	.I85	I.07	.480	TAPE MOUNTED LARGE REEL										
D	I92020I3I	BS-942-B	I6-I4	BLUE	.087	.I99	.I85	I.07	----	LOOSE PIECE										
	I92020I30	BS-932-BBT	I6-I4	BLUE	.087	.I99	.I85	I.07	.480	TAPE MOUNTED LARGE REEL										
	I92020045	CS-952	I2-I0	YELLOW	.I38	.276	.262	I.I5	----	LOOSE PIECE										
	I92020046	CS-952-DK	I2-I0	DARK YELLOW	.I38	.276	.262	I.I5	----	LOOSE PIECE										
	I92020047	CS-952-DKT	I2-I0	DARK YELLOW	.I38	.276	.262	I.I5	.440	TAPE MOUNTED										
C	I92020048	CS-952-DKBT	I2-I0	DARK YELLOW	.I38	.276	.262	I.I5	.440	TAPE MOUNTED LARGE REEL										
	I92020I4I	CS-952 BULK	I2-I0	YELLOW	.I38	.276	.262	I.I5	----	BULK PACKED, 2500 PER PACKAGE										
	I92020I42	CS-952-DK BULK	I2-I0	DARK YELLOW	.I38	.276	.262	I.I5	----	BULK PACKED, 2500 PER PACKAGE										