

REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL42002-R Series Housing.

Accepts AWG #28~18 Wire Range.

Insulation O.D.=0.9~3.1 mm.

Material : Phosphor Bronze .

Finish: Tin plated.

Thickness: 0.2 mm.

ORDERING INFORMATION

DLXXXXX - $\frac{XX}{1}$ - $\frac{X}{2}$ - $\frac{X}{3}$ - $\frac{X}{4}$ - $\frac{X}{5}$ - $\frac{XX}{6}$

1. PART NO.
2. TERMINAL CODE
3. MATERIAL TYPE: 1: PHOSPHOR BRONZE 2: BRASS 3: IRON
4: STAINLESS STEEL 5: OTHER
4. TECHNICS: 0: UNPLATED 1: FIRST PLATING 2: POST PLATING
3: OTHER
5. FINISH: 1: TIN-PLATED 2: MATTE PLATED 3: NICKEL PLATED
4: PICKLING 5: SILVER PLATED 6: GOLD PLATED
7: GALVANIZED 8: OTHER
6. SERIAL NUMBER: 00.01.02.....

TYPE	Dimension mm				Qty/Reel	适用线规 AWG#
	A1	B1	A2	B2		
5558-RT-01	3.6	3.8	2.2	2.7	5,000 PCS	24-18
5558-RT	3.6	3.8	2.0	2.1	5,000 PCS	28-20

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	.X° : ± 3.0°	PRODUCT NAME: DL42002-RT (5558-RT)		TITLE: 4.2mm Pitch Wire To Wire Crimp Terminal	
.XX: ± 0.15	.X° : ± 2.0°			PART NO: DL42002-RT-X-X-X-XX	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:2021/9/27	SCALE: N/A	
FINISH:		CHKD: Wu Hui	DATE:2021/9/27	PAGE: 1/2	
DRAWING NO: GC-DL42002-RT-X-X-X-XX		APPD:Ren An De	DATE:2021/9/27	UNITS: mm	REV.: A



