

K24LOC-P30LJG0-130S
series_l
type_k2




General information

Part number	K24LOC-P30LJG0-130S
Termination	solder
Size	4
Locking principle	break , push
Coding	0_key
Cable Diameter	cable_mini_13
Cable outlet	bend_relief



Illustrations may differ from original product.
Dimensions, unless otherwise specified, in mm.



Contact insert description

Number of contacts	30
Contact type	sockets
Contact diameter	09mm
Insulator material	peek
Wire cross section	22_awg
Termination	solder
Termination diameter	085mm

reverse_gender_on_request

Technical information

Max. creepage and air clearance distance	08_mm	17_mm
Nominal current single contact	075_a	iec_60512_5_2
Test voltage	1575_kv_ac	sae_13441

safety_text

Mechanical and environmental data

Degree of protection*	ip50
Operating temperature	40_120_c
Mating cycles	5000

mated_unmated

Material and surface treatments

Housing	m_chrome
Contact	cu_alloy_gold

safety_text_2
ul_text
illustrative_text