

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/16/21	
A		UPDATED SPEC.	4/24/23	JJ/AC

MMI-MOPXXXSXXB-IP68



CODING
1 = CODE 1
2 = CODE 2
3 = CODE 3

CABLE COLLET SIZE
32 = 2.2mm ~ 3.2mm ID
42 = 3.2mm ~ 4.2mm ID
52 = 4.2mm ~ 5.2mm ID


OF POSITIONS
02, 03, 04, 05,
& 07, 09

NOTE: BEND RELIEF
MUST BE ORDERED
SEPARATELY
SEE MMI-BR0-XX-XX-X

CODING OPTIONS		
CODE 1	CODE 2	CODE 3



DETAIL



CABLE COLLET

	2 Pin	3 Pin	4 Pin	5 Pin	7 Pin	9 Pin
Configuration						
Diameter of Pin	Ø0.9	Ø0.9	Ø0.7	Ø0.7	Ø0.5	Ø0.5
Testing Voltage	1200V	1100V	900V	900V	700V	500V
Working Voltage	350V	300V	250V	250V	200V	150V
Rated Current / Pin	8A	8A	5A	5A	3A	3A
Max. Wire Awg	22	22	24	24	28	28

SPECIFICATIONS:

Material:
Housing (Body): Brass, Natural Chrome plated
Insulator: PPS
Terminal: Brass, Gold Plated
Shell: Brass
Electrical:
Voltage Rating: See chart
Current Rating: See chart
Dielectric withstanding voltage: See chart
Electrical Life: 5,000 Cycles min.
Temperature Rating:
Operating temperature: -55°C to +150°C
Environmental:
IP68 Protection (Mated Condition)
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	SS	8/16/21
CHECKED	SS	8/16/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
PUSH-PULL CONNECTOR MALE PLUG, METAL, SIZE 0,
SOLDER TERMINAL, BEND RELIEF TYPE, IP68

SIZE X	PART NO. MMI-MOPXXXSXXB-IP68	REV. A
REF: XXXXX	SCALE: NTS	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MMI-M0P105S52B-IP68](#) [MMI-M0P103S52B-IP68](#) [MMI-M0P104S52B-IP68](#) [MMI-M0P107S52B-IP68](#) [MMI-M0P102S52B-IP68](#)