

## Han 3A-GW-M20 (150er Verp.)



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0620 XL
Specification	Han 3A-GW-M20 (150er Verp.)
HARTING eCatalogue	<a href="https://b2b.harting.com/19200030620XL">https://b2b.harting.com/19200030620XL</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A®
Type of hood/housing	Hood

### Version

Size	3 A
Version	Side entry
Cable entry	1x M20
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Polycarbonate (PC)
-------------------------	--------------------

## Material properties

Colour (hood/housing)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	150
Net weight	15.22 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140164215
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors