



Pushing Performance
Since 1945

Han 3A-HTE, 2 x 6-8mm, PA black



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 003 0422
Specification	Han 3A-HTE, 2 x 6-8mm, PA black
HARTING eCatalogue	https://b2b.harting.com/19200030422

Identification

Category	Hoods/Housings
Series of hoods/housings	Han A [®]
Type of hood/housing	Hood
Description of hood/housing	With integrated cable gland 2x Ø6 - 8

Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x Integrated
Locking type	Single locking lever
Field of application	Standard Hoods/housings for industrial applications
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	4 4X 12



Pushing Performance
Since 1945

Technical characteristics

Cable diameter	6 ... 8 mm
	6 ... 8 mm

Material properties

Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
Approvals	CE
	DNV GL

Commercial data

Packaging size	10
Net weight	17 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140569546
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors