



Pushing Performance  
Since 1945

# Han 24HPR EasyCon PE Modular Frame A-H



Image is for illustration purposes only. Please refer to product description.

Part number	09 40 024 9933
Specification	Han 24HPR EasyCon PE Modular Frame A-H
HARTING eCatalogue	<a href="https://b2b.harting.com/09400249933">https://b2b.harting.com/09400249933</a>

## Identification

Category	Accessories
Series of hoods/housings	Han® HPR EasyCon
Type of accessory	Frame
Description of the accessory	for up to 8 single modules A ... H

## Version

Size	24 B
Pack contents	1x male PE adapter 1x female PE adapter 2x M4/M5 distance bolts (AF 7) 2x M5/M6 distance bolts (AF 7) 2x M3 screw 2x M4 screw 2x washer SK S4

## Technical characteristics

Conductor cross-section	4 ... 10 mm² PE terminal power side 1 ... 2.5 mm² PE terminal signal side
Tightening torque	0.5 Nm Fixing screws M3 1.5 Nm Fixing screws M4 6 Nm Distance bolt 0.8 Nm PE terminal clamp 1 ... 2.5 mm2 1.5 Nm PE terminal clamp 4 ... 10 mm2
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



**Pushing Performance**  
Since 1945

## Material properties

Material (accessories)	Zinc die-cast Stainless steel
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	a4a9de28-6060-4c0d-b79b-5842f7db41be
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	1
Net weight	130 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140194458
ETIM	EC002310
eCl@ss	27440210 Fixing element for industrial connectors