

[illegible]

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/8	/	300/8
IEC Standard			
Overvoltage Category/Pollution Degree	III/3	III/2	II/2
Rated Voltage(V)/Current(A)	/	/	250/7
Rate Impulse Voltage(KV)	/	/	2.5
Pitch(mm)/Poles	3.81/N=04~48P		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		

4	Cover	PA66	UL94V-0
3	Pin 2	Copper Alloy	Sn Plated
2	Pin 1	Copper Alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					
DIM. TOL. X X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 GENERAL ANGLE: ±3°		TITLE: <i>Socket-type terminal</i>					
		DWG. NO.: JCB381-WDMCNP				DRAWN: MAX	
		PART NO.: JCB381-WDMCNP				CHECKED: ELLA	
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxcnnc	APPROVED: WILL

