

Part Number : 936030074

Product Description : Gwconnect D-Sub Gender Changer, Female-to-Female. 9 Poles

Series Number : 93606

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Number : 2500.0002.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Heavy-Duty Connectors
Series	93606
Description	Gwconnect D-Sub Gender Changer, Female-to-Female. 9 Poles
Component Type	Gender Changer (D-sub)
Product Family	GWconnect Heavy Duty Connectors (HDC)
Product Name	GWconnect
Standard	DIN 41652, IEC 60807
UPC	887191846156

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V AC / 150V DC

Physical

Gender	Female-Female
Lock to Mating Part	Yes
Net Weight	11.000/g
Packaging Type	Bag
Poles	9
Temperature Range - Operating	-25° to +125°C

Kit Component Parts

This document was generated on Oct 14, 2024