

Harax PG 13,5/ panel feed through / 3-po



Image is for illustration purposes only. Please refer to product description.

Part number	21 01 130 3013
Specification	Harax PG 13,5/ panel feed through / 3-po
HARTING eCatalogue	https://b2b.harting.com/21011303013

Identification

Category	Connectors
Series	HARAX®
Element	Panel feed through
Specification	With faston blades for front mounting

Version

Termination method	HARAX® connection technology
Shielding	Unshielded
Number of contacts	2
PE contact	Yes

Technical characteristics

Conductor cross-section	0.75 ... 1.5 mm²
Conductor cross-section	AWG 18 ... AWG 16
Wire outer diameter	≤2.8 mm
Rated current	16 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	>10 ⁸ Ω



Pushing Performance
Since 1945

Technical characteristics

Contact resistance	≤10 mΩ
Limiting temperature	-25 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Size	Pg 13.5
Cable diameter	6 ... 9 mm
Isolation group	I (600 ≤ CTI)

Material properties

Material (insert)	Polyamide (PA)
	Thermoplastic polyurethane (TPU)
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
Material (hood/housing)	Polyamide (PA)
	Thermoplastic polyurethane (TPU)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
	Naphthalene

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079

Commercial data

Packaging size	1
Net weight	24 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140136762



Pushing Performance
Since 1945

Commercial data

eCl@ss

27440103 Sensor-actuator connector chassis (sensor technology actuator)
