

M8 connector for ET connection, 4-pole, shielded



General information	
Product type designation	Connection plug
Product description	M8 plug connector with high degree of protection, 4-pin, metal version
Suitability for use	for connecting ET-CONNECTION nodes (e.g. SIMATIC ET 200AL) in degree of protection IP65 / 67
Degree and class of protection	
IP degree of protection	IP65/67
Ambient conditions	
Ambient temperature during assembly, min.	-30 °C
Ambient temperature during assembly, max.	80 °C
Ambient temperature during storage/transportation	
• min.	-40 °C
• max.	80 °C
Mechanics/material	
Outgoing feeder type	180° cable outlet
Material of housing	metal
Dimensions	
Width	14 mm
Depth	47 mm

last modified: 2/10/2021 