







THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1770139	2017-07-08	Frank Deng	Change Color of Gasket



With Liquid Glue



Pin Assignments
Front View



Recommended Panel Cut-out

Note:

- * $\varnothing$ Important Dimension To Check.
- * Waterproof Rate: IP68
- * Working Voltage Rating: AC 300 V
- * Working Current Rating: 5A
- * Flame Class: UL94V-0 (UV Resistance)
- * Housing: Nylon+GF, Black
- * Male Pin: Copper Alloy, Gold Plated
- * Nut: Nylon+GF, Black
- * Gasket: Silicone, Gray
- * Panel Thickness Max: 4.5mm

UNIT:mm TOLERANCE X ±0.25	TITLE X Lok B-Size Receptacle M Conn M 7 Pin		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO BD-07RMMS-QC8001	DRAWN BY Frank Deng	DATE 2017-07-08
	SCALE 2:1	SIZE A4			DWG NO BD-07RMMS-QC8001	CHECKED BY Fisher Wang	DATE 2017-07-08
	REV. B	WC-REV. A.3			CUSTOMER ALTW	APPROVED BY Kevin Hu	DATE 2017-07-08
SHEET 1 OF 1 QC: Inspection item				8 FMW10702-01-02A1			