





REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 01 through 01 Circuits.
Mates with DL80005-Y Series Housing.
Material : Nylon UL94V-0 (2) .
Ø2.36mm Square Pin.
Pin Material : Brass / Tin-Plated.



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL80005 (HP2. 2. 36) -1A	TITLE: 8.0....5.0 mm Pitch Wire To Board Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Yuan Jun Rong	DATE:21/08/01
.XXX: ± 0.01	.XX° : ± 1.0°	DATE:21/08/01	PART NO:
FINISH:		CHKD:Wu Hui	SCALE: N/A
DRAWING NO:		DATE:21/08/01	PAGE: 1/1
		UNITS: mm	REV. : A0


7		8	
REV.	REVISION DESCRIPTION	DATE	APPD




NOTES

Available in 02 through 02 Circuits.
Mates with DL80005-Y Series Housing.
Material : Nylon UL94V-0 (2) .
Ø2.36mm Square Pin.
Pin Material : Brass / Tin-Plated.



GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: ± 3.0°	PRODUCT NAME: DL80005 (HP2.36) -2A		TITLE: 8.0...5.0 mm Pitch Wire To Board Housing	
.XX: ± 0.15	.X°: ± 2.0°				
.XXX: ± 0.01	.XX°: ± 1.0°	DR: Yuan Jun Rong	DATE: 21/08/01	PART NO:	
FINISH: _____		CHKD: Wu Hui	DATE: 21/08/01		
DRAWING NO:	APPD: Ren An De	DATE: 21/08/01	UNITS: mm	SCALE: N/A	PAGE: 1/1
				REV.: AO	




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 03 through 03 Circuits.
Mates with DL80005-Y Series Housing.
Material : Nylon UL94V-0 (2) .
Ø2.36mm Square Pin.
Pin Material : Brass / Tin-Plated.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL80005 (HP2.36)-3A	TITLE: 8.0...5.0 mm Pitch Wire To Board Housing
.XX: ± 0.15	.X° : ± 2.0°		
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Yuan Jun Rong	DATE:21/08/01
FINISH:		CHKD:Wu Hui	DATE:21/08/01
DRAWING NO:		APPD:Ren An De	DATE:21/08/01
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A0




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 01.02 Circuits.
Mates with DL80005-A Series WAFER.
Material : Nylon UL94V-0(2).
Accepts DL80005-T Crimp Terminal.

Circuits	Type	Dimension mm	
		A	B
1	HP2.36-1Y	-	7.3
2	HP2.36-2Y	8.0	15.55

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE: 8.0....5.0 mm pitch WTB Connector Housing	
.XX: ± 0.15	.X° : ± 2.0°	DL80005 (HP2.36) -Y		PART NO:	
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Yuan Jun Rong	DATE: 21.08.01	SCALE: N/A	
FINISH: _____		CHKD: Wu Hui	DATE: 21.08.01	PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 21.08.01	UNITS: mm	REV. : A




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 03 Circuits.
Mates with DL80005-A Series WAFER.
Material : Nylon UL94V-0(2).
Accepts DL80005-T Crimp Terminal.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL80005 (HP2. 36) -3Y	TITLE: 8.0....5.0 mm pitch WTB Connector Housing
.XX: ± 0.15	.X° : ± 2.0°	DR: Yuan Jun Rong	DATE: 21.08.01
.XXX: ± 0.01	.XX° : ± 1.0°	DATE: 21.08.01	PART NO:
FINISH: _____		CHKD: Wu Hui	SCALE: N/A
DRAWING NO:		DATE: 21.08.01	PAGE: 1/1
		APPD: Ren An De	UNITS: mm
			REV. : A



NOTES

Used in DL80005-Y Series Housing.
Accepts AWG #24~18 Wire Range.
Insulation O.D.=1.7~3.0 mm.
Material : Phosphor Bronze .
Finish: Tin plated.
Thickness: 0.25 mm.

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : $\pm 3.0^\circ$	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : $\pm 2.0^\circ$	DL80005 (HP2.36)-T		8.00...5.0 mm Pitch Wire To Board Terminal	
.XXX: ± 0.01	.XX° : $\pm 1.0^\circ$	DR: Yuan Jun Rong	DATE:21.8.1	PART NO:	
FINISH:		CHKD:Wu Hui	DATE:21.8.1	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD:Ren An De	DATE:21.8.1	UNITS: mm	REV.: A