




PIN NO.	A	B	C	D
8	15.60	6.00	13.45	7.00
12	19.60	10.00	17.45	11.00
16	23.60	14.00	21.45	15.00
20	27.60	18.00	25.45	19.00
24	31.60	22.00	29.45	23.00
28	35.60	26.00	33.45	27.00
32	39.60	30.00	37.45	31.00
40	47.60	38.00	45.45	39.00



ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

NO.: X332X W R S-XXX-PP SN XX
 ① ② ③ ④ ⑤⑥ ⑦ ⑧ ⑨

- 1.Series No:332A—TYPE A
332B—TYPE B
332C—TYPE C
- 2.Category:W—Wafer
- 3.Welding Board Angle:R—Stright 90°
- 4.Welding Way:S—SMT
- 5.Row No.Pin No:XX—See Table A
- 6.Morphology:Blank—No CPA Feature
C—With CPA Feature
- 7.Material:PP—PPS
- 8.Plating Category:SN—Tin Plating
- 9.Color:Blank—Black; GR—Gray;
BL—Blue

X332CWRS-XX-PPSNXX	X332CH-XX	X332XT-BSN	No CPA Feature
X332BWRS-XX-PPSNXX	X332BH-XX	X332XT-BSN	No CPA Feature
X332AWRS-XX-PPSNXX	X332AH-XX	X332XT-BSN	No CPA Feature
X332CWRS-XXC-PPSNXX	X332CH-XXC	X332XT-BSN	With CPA Feature
X332BWRS-XXC-PPSNXX	X332BH-XXC	X332XT-BSN	With CPA Feature
X332AWRS-XXC-PPSNXX	X332AH-XXC	X332XT-BSN	With CPA Feature
PART NO.	Suitable XKB HOUSING	Suitable XKB Terminal	NOTE


4	SOLDERING PIN	2	COPPER ALLOY	MATTE TIN PLATED,OVER NICKEL
3	CONTACT PIN	N/2	COPPER ALLOY	
2	CONTACT PIN	N/2	COPPER ALLOY	
1	HOUSING	1	PPS BLACK	
ITEM	PART NAME	Q'TY	MATERIAL	FINISH



XKB INDUSTRIAL PRECISION CO.,LIMITED

MODEL TYPE:	2.0mm Crimp Style Wafer		
PART NO.:	X332XWRS-XXX-PPSNXX		
DWG NO.:			
SCALE	PAGE	REVISION	
N/A	1/3	A0	

	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.07.17	桑 菴



PCB THICKNESS:1.6mm
TOLERANCE±0.05
(TOP VIEW)

