

Triple-Gang French-Style Gang Frame, White, TAA

MODEL NUMBER: **N042F-WF3**



French-style gang frame accepts compatible wall-mount inserts for terminating premise audio/video, voice or data applications.

Features

French Gang Frame Connects Your In-Wall Audio/Video, Voice or Data Cable Line

This gang frame for mounting or trunking is ideal for terminating your premise wiring applications, including home theater, VoIP phones and Ethernet. The French-style N042F-WF3 protects electrical and network cables to help prevent accidental damage to your application. It's compatible with N042E-WM1-S unloaded shuttered module and N042E-WHM0 blank insert (sold separately).

High-Impact Construction Designed to Blend In Seamlessly with Your Room

This white cover plate measures 80 x 175 millimeters (outer frame) and fits three 45 x 45 millimeter modules. It helps hide unattractive cabling and blends elegantly into any home or office décor for a sleek, professional installation. The ABS plastic construction meets UL 94V-0 flame-retardant standards for protection against fire and high heat.

TAA-Compliant for GSA Schedule Purchases

The N042F-WF3 is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Ideal for home theater, VoIP or Ethernet in-wall wiring installations
- Helps prevent accidental cable damage and hides unattractive wiring
- Compatible with select N042E-Series modules and inserts (sold separately)
- High-impact plastic construction designed to blend in with your home/office décor
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

N042F-WF3 Triple-Gang French-Style Gang Frame, White, TAA

Specifications

OVERVIEW	
UPC Code	037332268976
Accessory Type	Wall Plate
Technology	Cat5/5e; Cat6; Cat6a; DisplayPort; HDBaseT; HDMI; USB
Country/Region	France
PHYSICAL	
Color	White



Powering Business Worldwide

TRIPP LITE
SERIES

Material of Construction	ABS
Total Number of Ports	0
Unit Dimensions (hwd / in.)	6.910 x 3.150 x 0.790
Unit Dimensions (hwd / mm)	OUTER: 175.5 x 80 x 20; INNER: 135 X 1.78
Finish	Matte
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-40° to 154°F (-40° to 68°C)
Operating Humidity Range	10% to 90% RH, (Non-Condensing)
Storage Humidity Range	10% to 90% RH, (Non-Condensing)
FEATURES & SPECIFICATIONS	
Antibacterial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.